

---

## 20 AMP NEMA CONNECTOR L720 - BLACK BACK, WHITE FRONT BODY

L720C | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Connector 3wire 20amp 480volt Turnlok



**PRODUCT**  
ENVIRONMENTAL PROFILE

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Black, White

Type: Connector

Number Of Wires: 3

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Standard: Yes

CUL Listing No: No

cULus: Yes

cURus: No  
Federal Spec: Yes  
UL Listing No: 498  
UL Standard: Yes  
UN SPSC: 39121403  
UR: No

#### **DIMENSIONS**

Depth (US): 2.20"  
Length (US): 3.33"

#### **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: L720  
Volts: 480V  
Volts (AC): 480

#### **COUNTRY OF ORIGIN**

Country Of Origin: MEXICO