



S9390

18W/LED/HID/5000K/100-277V E26
18 watt - LED HID Replacement; 5000K; Medium base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum Compartment Size		
Length	Width	Depth
8.5 inch	6 inch	6 inch

Optional accessory: In-line surge protector [80-929](#)

This item has been discontinued.
Possible replacement:

- [S29390](#)



S9390

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9390	Hi-Pro	045923093906	100 - 277	18	120W	32W	70W

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Medium	E26	18W/LED/HID/5000K/100-277V E26	Non-Dimmable	White	6-7/8"	2-3/4"	2400
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
50000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)	48	Box
RoHS Compliant	UL or ETL Listed	Warranty	Status	Suggested Substitute			
Yes	Yes	5 Year Limited	Discontinued	S29390			



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

