



# S9394

54W/LED/HID/5000K/100-277V  
54 watt - LED HID Replacement; 5000K; Mogul extended base;  
100-277 volts

### Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- DLC Listed
- Base up or base down operation (high/low bay and post top)
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C

### Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Minimum Compartment Size		
Length	Width	Depth
17.3 inch	9.25 inch	9.25 inch

Optional accessory: In-line surge protector [80-929](#)

This item has been discontinued.  
Possible replacement:

- [S29394](#)



S9394

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9394	Hi-Pro	045923093944	100 - 277	54	300W	85W	250W

Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Mogul Extended	EX39	54W/LED/HID/5000K/100-277V		Non-Dimmable	White	10-3/4"	3.69"	7200
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack	Package Type
50000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)		12	Box
DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification	Warranty	Status	Suggested Substitute		
P7RMM9YA; PMM9NX2Z <a href="#">DLC Search</a>	Yes	Yes	cULus - Damp Location Rated	<a href="#">5 Year Limited</a>	Discontinued	<a href="#">S29394</a>		



**National Toll-Free:**  
 800.43.SATCO  
 (800.437.2826)  
[www.satco.com](http://www.satco.com)

**Distribution Centers:**  
 New York, Florida, Texas,  
 Washington, California,  
 Puerto Rico

**Corporate Offices:**  
 110 Heartland Blvd.,  
 Brentwood, NY 11717  
 800.437.2826 631.243.2022  
 Fax 631.243.2027

