



S9396

100W/LED/HID/5000K/100-277V/EX39
100 watt - LED HID Replacement (up to 400W); 5000K; Mogul
extended base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP65 rated
- For outdoor & indoor use
- DLC Listed
- Base up or base down operation (high/low bay and post top)
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- Classified under UL 1598C
- Safety chain included

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V
- Built in surge protection

Minimum Compartment Size		
Length	Width	Depth
17.3 inch	9.25 inch	9.25 inch

Optional accessory: In-line surge protector [80-929](#)

This item has been discontinued.
Possible replacement:

- [S29396](#)



S9396

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
-------------	--------------	-----	---------------	-------	-------------------------	------------------------	----------------

S9396	Hi-Pro	045923093968	100 - 277	100	500W	150W	400W	
Base	ANSI Base	Lamp Code		Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Mogul Extended	EX39	100W/LED/HID/5000K/100-277V/EX39		Non-Dimmable	White	9-5/8"	5.87"	13300
Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature		Pack	Package Type
50000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)		4	Box
DLC ID:	RoHS Compliant	UL or ETL Listed	UL Classification		Warranty	Status	Suggested Substitute	
P93FAQCD; PE62TJJC DLC Search	Yes	Yes	cULus - Damp Location Rated		5 Year Limited	Discontinued	S29396	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

