## Technical Information Bulletin





Date:	Name of distributor:	
In hands date of project:	Client #:	
Project name/Number:	Name of end user:	

## ORDERING INFORMATION

Order code: 66267

Description: A19/6W/27K/ND/CHOICE/STD

UPC: 69549662674

Case quantity: 6 / 48

## PERFORMANCE DATA

Shape: A19 Base: E26 Watts(W): Volts (VAC): 120 Colour temperature (K)\*\*: 2 700 Average life (L70 hours): 15 000 Initial lumens (lm)\*: 506 Initial lumens per watt (lm/W): 84 CRI: 81 Beam angle: 220 Power factor: 0.6

-20 °C to 45 °C (-4 °F to 113 °F) Operating temperature range:

\*Initial lumens range: +/- 10 %

\*\*Typical colour temperature range: +/- 5 %

























## **CAUTIONS**

- Turn power off before inspection, installation, or removal.
  Risk of electrical shock do not use where directly exposed to water or weather.
  Suitable for use in totally enclosed luminaires.
  Suitable for use in damp locations.
  Do not open no user serviceable parts inside.
  Use only on 120 VAC, 60Hz circuits.
  This device is not intended for use with emergency exit fixtures or emergency exit lights.
  Do not use with dimmers.

For complete warranty information visit  3 Years Limited Warranty.	www.standardpro.com.

Qty	Description	Price	
I accept the spe	ecifications of the luminaire configuration	n mentioned above.	
Name:			
Company:			
Signature:		Date:	