Technical Information Bulletin CHOICE LED Lamps



Date:	Name of distributor:
In hands date of project:	Client #:
Project name/Number:	Name of end user:

ORDERING INFORMATION

Order code:	66286
Description:	P30L/12W/27K/40/CHOICE/STD
UPC:	69549662865
Case quantity:	6



COMPATIBLE DIMMERS

HCL453P

IPL06

AAL06, DAL06P, SLC03P

MACL-153P, PD-6WCL

6615, 6674, DSL06-1LZ, DSM10-1LZ,

AYCL-253P, CTCL-153P, DVCL-253P,

Legrand

Cooper

Leviton

Lutron

PERFORMANCE DATA

Shape:	PAR30LN
Base:	E26
Watts(W):	12
Volts (VAC):	120
Colour temperature (K)**:	2 700
Life L70 (hrs):	15 000
Initial lumens (lm)*:	935
Initial lumens per watt (lm/W):	78
CRI:	92
Beam angle (°):	40
CBCP:	1 813
Power factor:	0.93
Operating temperature range:	-20 °C to 40 °C (-4 °F to 104 °F)
Traditional equivalent (W):	75

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 10 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock do not use where directly exposed to water or weather. Not for use in totally enclosed luminaires.
- Suitable for use in wet locations.
- Do not open no user serviceable parts inside.
 Use only on 120 VAC, 60Hz circuits.
 This device is not intended for use with emergency exit fixtures or emergency exit lights.
- · Compatible with most dimmers.
- · For complete dimmer and warranty information visit www.standardpro.com.

Qty	Description	Price			
I accept the specifications of the luminaire configuration mentioned above.					
Name:					
Company:					
Signature:		Date:			

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.