

Catalogue no.	Size	Lamp/Watts	Voltage	Ballast	Service Quantity		Appl. Page
					2 days	10 days	

Recessed

LP3 - See Cross Reference Guide (Page 9)

2LP3GA332-36AL-347-1/3-EB	2'x4'	3-T8/32	347	T8 ELECT.	35		
2LP3GA332-36AL-UNV-1/3-EB	2'x4'	3-T8/32	120/277	T8 ELECT.	35		15
2LP3GA231U6R-33AL-UNV-1/2-EB	2'x4'	2-T8U6/31	120/277	T8 ELECT.	25		13, 15

TG8 Series Troffer 1'x4' - Formerly AA Series Troffer 1'x4' - See Cross Reference Guide (Page 9)

1TG8232-01-UNV-1/2-EB	1'x4'	2-T8/32	120/277	T8 ELECT.	120		13, 15
1TG8232-01-347-1/2-EB	1'x4'	2-T8/32	347	T8 ELECT.	90		

TG8 Series Troffer 2'x2' - Formerly AA Series Troffer 2'x2' - See Cross Reference Guide (Page 9)

2TG8231U6R-01-UNV-1/2-EB	2'x2'	2-T8U6/32	120/277	T8 ELECT.	80		13, 15
2TG8231U6R-01-347-1/2-EB	2'x2'	2-T8U6/32	347	T8 ELECT.	52		

TG8 Series Troffer 2'x4' - Formerly AA Series Troffer 2'x4' - See Cross Reference Guide (Page 9)

2TG8232-01-UNV-1/2-EB	2'x4'	2-T8/32	120/277	T8 ELECT.	52		13, 15
2TG8232-01-347-1/2-EB	2'x4'	2-T8/32	347	T8 ELECT.	52		
2TG8332-01-UNV-1/3-EB	2'x4'	3-T8/32	120/277	T8 ELECT.	78		15
2TG8332-01-347-1/3-EB	2'x4'	3-T8/32	347	T8 ELECT.	52		
2TG8432-01-UNV-1/4-EB	2'x4'	4-T8/32	120/277	T8 ELECT.	150		15
2TG8432-01-347-1/4-EB	2'x4'	4-T8/32	347	T8 ELECT.	104		

LED T-Grid LED Troffer

2TG38L840-2-FS-02F-UNV	2'x2'	3800lms/4000K	120/277	0-10v dim	35		
2TG45L840-2-FS-02F-UNV	2'x2'	4500lms/4000K	120/277	0-10v dim	35		
2TG48L840-4-FS-02F-UNV	2'x4'	4800lms/4000K	120/277	0-10v dim	35		
2TG54L840-4-FS-02F-UNV	2'x4'	5400lms/4000K	120/277	0-10v dim	35		
2TG74L840-4-FS-02F-UNV	2'x4'	7400lms/4000K	120/277	0-10v dim	35		

Surface

SMR Surface Modular 1'x4' - Formerly Surface SLB Series 1'x4' - See Cross Reference Guide (Page 11)

1SMR232-FA01-UNV-1/2-EB	1'x4'	2-T8/32	120/277	T8 ELECT.	35		14
1SMR232-FA01-347-1/2-EB	1'x4'	2-T8/32	347	T8 ELECT.		30	

SMR Surface Modular 2'x4' - Formerly Surface SLB Series 2'x4' - See Cross Reference Guide (Page 11)

2SMR432-FS01-UNV-1/4-EB	2'x4'	4-T8/32	120/277	T8 ELECT.	25		
-------------------------	-------	---------	---------	-----------	----	--	--

OW Wrap - Formerly TX Series Surface Wrap - See Cross Reference Guide (Page 11)

OWN232-UNV-1/2-EB	8-5/8"x48"	2-T8/32	120/277	T8 ELECT.	88		14
OWN232-347-1/2-EB	8-5/8"x48"	2-T8/32	347	T8 ELECT.	56		
OWW432-UNV-1/4-EB	13-7/8"x48"	4-T8/32	120/277	T8 ELECT.	36		14

CSW Cubelite

CSW148-UNVHIZO	4"x48"	1-T8/32	120/277	T8 ELECT.	35		
CSW248-UNVHIZO	4"x48"	2-T8/32	120/277	T8 ELECT.	35		

