



Catalog Number
Notes
Type

Contractor Select™

IBE

LED High Bay Light



The right selection for your basic, affordable warehouse lighting - the I-BEAM® IBE LED luminaire gives budget-conscious customers a reliable LED solution featuring 6kV surge protection standard. The I-BEAM® IBE LED is designed to meet the challenges of warehouse and light industrial applications.

FEATURES:

- Robust 6kV surge protection standard, meeting the ANSI standard for Industrial Environments
- UL listed to 45°C ambient with a thermal management system allowing for safe operation during times when temperatures rise up to 55°C*
- Save up to 60% in energy and maintenance costs over traditional sources



*Prolonged use at 55°C may impact long-term performance

Catalog Number	UPC	Description	Lumens	Input Watts	CCT	Voltage	Distribution	Pallet Qty.
IBE 12LM MVOLT 40K	00191848491010	IBE LED High Bay	11,306	85.2W	4000K	120-277V	Medium	48
IBE 12LM MVOLT 50K	00191848491096	IBE LED High Bay	11,652	85.2W	5000K	120-277V	Medium	48
IBE 15LM MVOLT 40K	00191848491041	IBE LED High Bay	13,966	103.9W	4000K	120-277V	Medium	48
IBE 15LM MVOLT 50K	00191848491058	IBE LED High Bay	14,394	103.9W	5000K	120-277V	Medium	48
IBE 18LM MVOLT 40K	001918488491027	IBE LED High Bay	17,762	136.1W	4000K	120-277V	Medium	48
IBE 18LM MVOLT 50K	00191848491072	IBE LED High Bay	18,306	136.1W	5000K	120-277V	Medium	48
IBE 22LM MVOLT 40K	00191848491195	IBE LED High Bay	21,067	164.7W	4000K	120-277V	Medium	48
IBE 22LM MVOLT 50K	00191848491133	IBE LED High Bay	21,712	164.7W	5000K	120-277V	Medium	48

Accessories: Order as separate catalog number.	
Mounting	
IBAC120 M20	Aircraft cable 10' with hook (one pair)
IBAC240 M20	Aircraft cable 20' with hook (one pair)
IBLPMP	Pendant monopoint splice box, includes side covers
IBLPMPHB	Pendant monopoint splice box, includes side covers (3/4" hub)
HC36	Chain hangers (one pair, 36" long)
Wire guards	
WGIBE	Wire guard
WGIBE4	Wire guard for 18L and 24L fixtures