



233-20

233-21

(/Products/Work-Gear/Heated-Gear/Heated-Jackets/233-20)

M12™ Heated Women's AXIS™ Jacket Kit

★★★★★ (0) Write a review

The MILWAUKEE® M12™ Heated Women's AXIS™ Jackets are designed to protect from cold and weather on the jobsite. Powered by M12™ REDLITHIUM™ Battery Technology, these heated jacket kits use carbon fiber heating elements to create and distribute heat to the chest, back and shoulders. A single touch LED controller heats up the battery heated jacket to three heat settings, creating a comfortable heat for any environment. This MILWAUKEE® heated jacket kit has a new Quick-Heat function that creates and distributes heat three times faster than our previous women's jackets and market competitors. AXIS™ Ripstop Polyester provides a lightweight, compressible design

Read More

INCLUDES:

- (1) M12™ Heated Women's AXIS™ Jacket (233-20) (/Products/Work-Gear/Heated-Gear/Heated-Jackets/233-20)
- (1) M12™ REDLITHIUM™ CP2.0 Battery Pack (48-11-2420) (/Products/Batteries-and-Chargers/M12-Batteries-and-Chargers/48-11-2420)
- (1) M12™ Compact Charger and Power Source (48-59-1201) (/Products/Batteries-and-Chargers/M12-Batteries-and-Chargers/48-59-1201)

Color - Black



Size - S (233B-21S)

- | | | | | |
|---|---|---|----|----|
| S | M | L | XL | 2X |
|---|---|---|----|----|

Download Sizing Chart (/media/PDFs/Sizing-Charts/Milwaukee-Heated-Gear-Sizing-Guide-2018.ashx)

No Sellers Found

KEY FEATURES

SPECIFICATIONS

REVIEWS

M12™ HEATED AXIS JACKET



LIGHTWEIGHT INSULATED HEAT

AXIS™ RIPSTOP POLYESTER

- More Durable. Built To Layer.





