



PAR30/PAR20 LED

10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB

Philips PAR30 and PAR20 LED Single Optic Lamps provide superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	25000X
Technical Type	10-75W
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	25 °
Initial lumen (Nom)	800 lm
Luminous Flux (Rated) (Nom)	800 lm
Luminous Intensity (Nom)	3300 cd
Color Designation	Warm White (WW)
Rated Beam Angle	25 °
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	86 mA
Wattage Equivalent	75 W

Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	67 °C

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Suitable For Accent Lighting	Yes


Product Data	
Order product name	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB
EAN/UPC - Product	046677529703
Order code	529701
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001321504
Net Weight (Piece)	0.285 kg

PAR30/PAR20 LED

Warnings and Safety

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.
- CAUTION: Risk of electric shock— do not use where directly exposed to water
- NOTES: This device complies with Part 18 of the FCC rule. This product may cause interference with other devices. If interference occurs, change the location of the products involved. This RFLD device complies with Canadian ICES-005.


Dimensional drawing




Glass UL wet PAR30L 120V 9-75W 800lm 25D

Product	D	C
10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	94 mm	118 mm


Photometric data



10-75W E26 PAR30L





10-75W E26 PAR30L 25D 827 2700K



PAR30/PAR20 LED

Lifetime



14-120W E26 PAR38

14-120W E26 PAR38

