

### DESCRIPTION

M8 CV series remote gives you 6 modes with 7 color shortcut and 7 color save key, allowing over 300 different changing modes.

### FEATURES

- RF remote control
- 5A load per channel to a max of 20A
- 7 color save keys
- Programmable

### SPECIFICATIONS

- Power input: DC24V
- Max current load: 5A x 4CH Max 20A
- Max output power: 480W @ 24V
- Compatible remote: M1/M2/M3/M4/M5/M6/M7/M8
- GreyScale Max 4096 x 4096 x 4096 x 4096
- Diemensions: L175 x W44 x H30 (mm)

