

## M4 & M4-5A RGB REMOTE AND CONTROLLER

### DESCRIPTION

M4-5A CV series drivers give you 8 different RF remote controller options depending on your need.

### FEATURES

- RF remote control
- remotes can work up to 40-50m
- 5A load per channel to a max of 20A
- 8 different RF remote options depending on the use required

### SPECIFICATIONS

- Power input: DC24V
- Max current load: 5A x 4CH Max 20A
- Max output power: 480W @ 24V
- Compatible remote: M1/M2/M3/M4/M5/M6/M7/M8
- GreyScale Max 4096 x 4096 x 4096 x 4096
- Dimensions: L175 x W44 x H30 (mm)

