## **JA Series**

## 200 AMP SOCKET c/w Breaker



CATALOGUE #	DESCRIPTION	ENCLOSURE SIZE H X W X D	WEIGHT
JA402P	c/w 200 Amp breaker, 4 jaw, 120/240 VOLTS, single phase, 3 wire	30" x 10 <sup>1</sup> / <sub>4</sub> " x 5 <sup>1</sup> / <sub>4</sub> "	25 lbs.
JA402PSD-LB JA402PSD	as above, less breaker (will accomodate square D breaker only) c/w 200 amp square D breaker	30" x 10 <sup>1</sup> / <sub>4</sub> " x 5 <sup>1</sup> / <sub>4</sub> " 30" x 10 <sup>1</sup> / <sub>4</sub> " x 5 <sup>1</sup> / <sub>4</sub> "	24 lbs. 25 lbs.

- 200 Amp 120/240 VOLT
- Combination meter socket & circuit breaker
- CSA enclosure 3
- Conductor range #6 250 MCM CU/AL
- Suitable for temporary service, farm service, trailers, recreational parks, commercial and residential locations.
- Service entrance rated

- Also available with 125 Amp breaker of	or
150 Amp breaker upon request	

- Also	availa	hla	000	hraal	or
- AISO	CIVCIIICI	DIE I	<b>E33</b>	urear	Lei

50

KNOCKOUT	CONDUIT	
CODE	SIZE	
G	11/4", 11/2", 2", 21/2"	

