

# Technical Information Bulletin

## LED Puck Light



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
 In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
 Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 67171  
 Description: UCP/KIT3/12V/2.2W/40K/FR/WH/STD  
 UPC: 69549671713  
 Case quantity: 30

### PHYSICAL DATA

Type: LED Puck Light - kit of 3 units  
 Size (in): 3"  
 Shape: Round  
 Finish: White  
 Lens Finish: Frosted  
 Mounting: Surface and Recessed  
 Wire Length (ft.): 4  
 Wire gauge (AWG): 24  
 Daisy Chain installation: Up to 10 pucks can be installed in daisy chain



### PERFORMANCE DATA


Watts (W) per unit: 2.2  
 Volts (VDC): 12  
 Colour temp. (K)<sup>1</sup>: 4 000  
 Lumen output (lm) per unit: 150  
 Lumen per Watts (lm/W) per unit: 68  
 CRI: 90  
 Life L70 (h)<sup>2</sup>: 50 000  
 Beam angle (°): 120  
 Operating temp. range: -20°C to 40°C (-4°F to 104°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %

<sup>2</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations



### TECHNICAL DRAWINGS AND DIMENSIONS



### COMPATIBLE ACCESSORIES

Order code	Description	Type
67181	UCP/TRIM/BACKPLATE/BLK/STD	Black trim and back plate
67182	UCP/TRIM/BACKPLATE/BN/STD	Brushed nickel trim and back plate
67183	UCP/ACC/HUB6/STD	Hub for 6 LED Puck Lights
67185	UCP/ACC/DIMMER/STD	Dimmer Switch
67186	UCP/ACC/MOTIONSENSOR/STD	Motion Sensor

### COMPATIBLE DRIVERS

Order code	Description	*(Included in the kits of 3 units)
67184*	LED/DRIVER/12W/12V/PLUG/ND/STD	
62665	LED/TAPE/36W/12V/WW+CW/PS/ND/STD	
65743	LED/DRIVER/10W/12V/HW/ND/STD	
65744	LED/DRIVER/20W/12V/HW/ND/STD	
65740	LED/DRIVER/50W/12V/HW/D/STD	
65745	LED/DRIVER/60W/12V/HW/ND/VS/STD	
65746	LED/DRIVER/60W/12V/HW/ND/STD	
67071	DRIVER-DIMMER/12V/60W/WH/STD	

### DESCRIPTION AND OTHER OPTIONS

UCP	/	KIT3	/	12V	/	2.2W	/	40K	/	FR	/	WH	/	STD
Family		Kit		Volts		Watts		Colour Temperature		Lens Finish		Trim Colour		Brand
UCP Undercabinet Pucks		3 Kit of 3		12V 12 Volts		2.2W 2.2 Watts		30K 3 000 K 40K 4 000 K		FR Frosted		WH White BLK Black BN Brushed nickel		STD STANDARD

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_

Company: \_\_\_\_\_

Signature: \_\_\_\_\_

Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment and representative of relative performance.  
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.  
 February 14, 2019