



Data and specifications subject to change without notice

Project name	Type
Order number	
Date	

ECLIPSE

MR16 TRIM

SPECIFICATIONS

- ◆ Rotate 358° and adjust vertically up to 20°.
- ◆ Made of die-cast aluminum
- ◆ Powder coated or plated finishes
- ◆ Lamp holder accepts 1 lens accessory, clear glass lens included
- ◆ Optional matte black center lamp holder
- ◆ Trim & Housing combination are designed for typical 5/8" drywall application, contact factory for various ceiling thickness
- ◆ Soraa MR16 LED lamp compatible with E15 electronic transformer option only, available in 120V AC input only

MAX WATTAGE	TRANSFORMER					
	HOUSING	MAGNETIC	ELECTRONIC	E15-120	Q-TRAN	MPT
	2-010-I/C & A/T	50W	37W	15W	50W	50W
	2-012-I/C & A/T	n/a	n/a	n/a	50W	n/a
	2-020-F	50W	50W	15W	n/a	n/a
	2-020-F-D/A	50W	50W	15W	n/a	50W
	2-030-R	50W	50W	15W	50W	50W
	2-060-F	75W	75W	n/a	n/a	n/a
	2-060-F-D/A	75W	75W	n/a	75W	75W
	2-060-F-C/P	75W	75W	15W	n/a	n/a
	2-100-C/H	75W	75W	15W	n/a	n/a

ORDER GUIDE

HOUSING - CEILING - TRANSFORMER² - VOLTAGE

TRIM - FINISH - OPTION

HOUSING	CEILING	TRANSFORMER ²	VOLTAGE
2-010	I/C	(BLANK) - Magnetic	120
2-012	I/C-A/T	E - Electronic	277
		E15 - 15W Electronic ¹	347²
2-020	F	TOR - Q-Tran Magnetic	
	F-D/A	MPT - Magnetic Potted	
2-030	R		
2-060	F		
	F-D/A		
	F-C/P		
2-100	C/H		

TRIM	FINISH	OPTION
2-140 - Eclipse	01 - White	BC - Black Center
	02 - Chrome (Plated)	
	04 - Black	
	05 - Matte Silver	
	06 - Bronze	
	09 - Gold (Plated)	

Note:

- 1) Compatible with Soraa MR16 LED lamp, rated MAX 15Watts
Available in 120V AC input only
- 2) Refer to individual housing spec sheet for availability
- 3) "NO HOUSING" indicates use with a remote Class 2 transformer
Transformer and R12S socket sold separately
Only available in halogen MR16 lamps

*Spec sheets are subject to change without notice