

SK1-20



SK1-20 Signal Contact

General Information

Extended Product Type	SK1-20
Product ID	1SAM201903R1002
EAN	4013614320408
Catalog Description	SK1-20 Signal Contact
Long Description	SK1-20 Signaling Contact 2 NO

Ordering

Minimum Order Quantity	2 piece
Customs Tariff Number	85365080

Popular Downloads

Data Sheet, Technical Information	1SBC100192C02--
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802

Dimensions

Product Net Width	9 mm
Product Net Height	90 mm
Product Net Depth / Length	78.5 mm
Product Net Weight	0.035 kg

Technical

Terminal Type	Screw Terminals
Rated Operational Voltage	690 V AC 600 V DC Main Circuit 690 V
Rated Operational Current AC-15 (I_{th})	(240 V) 4 A (24 V) 6 A (380 / 400 V) 3 A (690 V) 1 A
Rated Operational Current DC-13 (I_{th})	(125 V) 0.55 A (24 V) 2 A (250 V) 0.27 A (440 V) 0.15 A

	(600 V) 0.15 A
Rated Impulse Withstand Voltage (U_{imp})	Auxiliary Circuit 6 kV
Rated Insulation Voltage (U_i)	690 V
Degree of Protection	IP20
Electrical Durability	100000 cycle
Mechanical Durability	100000 cycle
Connecting Capacity Auxiliary Circuit	Flexible with Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible with Insulated Ferrule 1/2x 0.75 ... 1.5 mm ² Flexible 1/2x 0.75 ... 1.5 mm ² Rigid 1/2x 1 ... 1.5 mm ²
Tightening Torque	Auxiliary Circuit 0.8 ... 1.2 N·m
Wire Stripping Length	Auxiliary Circuit 8 mm
Recommended Screw Driver	M3 Pozidriv 2
Number of Auxiliary Contacts NO	2
Number of Auxiliary Contacts NC	0
Standards	IEC/EN 60947-1 IEC/EN 60947-5-1 UL 60947-1 UL 60947-4-1 UL 508 CSA 22.2 No. 14
Product Name	Signal Contact
Suitable For	MS116 MS132 MO132 MS165 MO165
Suitable for Product Class	Manual Motor Starter
Accessory Group	Electrical
Accessory Type	Signal Contact

Environmental

Ambient Air Temperature	Operation -25 ... +60 °C Storage -50 ... +80 °C
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical UL/CSA

Maximum Operating Voltage UL/CSA	Main Circuit 600 V AC
Connecting Capacity Auxiliary Circuit UL/CSA	Flexible 1/2x 16-14 AWG Stranded 1/2x 16-14 AWG
Tightening Torque UL/CSA	Auxiliary Circuit 7 in·lb
Contact Rating UL/CSA	B600 Q600

Certificates and Declarations (Document Number)

ABS Certificate	1SAA963001-0101
BV Certificate	1SAA963002-0201
CB Certificate	1SAA963001-2002
CCC Certificate	1SAA963003-3802
cUL Certificate	cUL_E137861

Declaration of Conformity - CE	1SAD938500-0198 1SAD938500-0197 1SAD938510-0125 1SAD938502-0190 1SAD938501-0191 1SAD938502-0188
DNV GL Certificate	1SAA963001-0304
GOST Certificate	1SAA937000-2703
Instructions and Manuals	2CDC131011M6802 2CDC131034M6801 2CDC131022M6802
LR Certificate	1SAA963001-0502 1SAA918001-0501
RINA Certificate	1SAA963000-0802
RoHS Information	1SAA963001-4407
UL Certificate	UL_E137861

Container Information

Package Level 1 Width	25 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Height	93 mm
Package Level 1 Gross Weight	0.08 kg
Package Level 1 EAN	4013614481505
Package Level 1 Units	box 2 piece
Package Level 2 Width	280 mm
Package Level 2 Depth / Length	395 mm
Package Level 2 Height	210 mm
Package Level 2 Gross Weight	6.775 kg
Package Level 2 EAN	4013614523632
Package Level 2 Units	carton 160 piece

Classifications

Object Classification Code	Q
ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC000041 - Auxiliary contact block
ETIM 6	EC000041 - Auxiliary contact block
ETIM 7	EC000041 - Auxiliary contact block
eClass	7.0 27371302
UNSPSC	39121522

Categories

Low Voltage Products and Systems → Control Products → Manual Motor Starters → Manual Motor Starters Accessories

