

SLIM SURFACE LED

Round LED Slim Surface Mount Dimmable Fixture
with Easy Color SeleCCTor

1/2" Thick Surface LED Fixture

Catalog Number:

Project Name:

Note:

Type:



ENGINEERED FOR VERSATILITY AND PERFORMANCE

The Elite LED Slim Surface Mount has been engineered to install into most standard junction boxes. Up to 2000 usable lumens are directed from the luminaire to the work surface. Lighting is smooth and comfortable, all while using 75% less energy than the equivalent Incandescent. Features 50,000 hours of life, and California Title-24 compliance.

OPTICS

The Elite LED Module system is much more than just a simple LED retrofit. The Elite LED system is a highly engineered work of design and optical science which produces up to 2000 lumens. Our meticulously crafted optics gather the light scattered by the LED chip and shape it into a functional beam with uniform light distribution.

DIMMING

Intended for Triac (120V) base on configuration. Minimum 90° supply conductors.

WARRANTY

The Elite LED lighting system carries a five-year carefree warranty for parts and components. (Labor not included)



SPECIFICATIONS:

APERTURE	7"	9"	11"
LUMENS	1000 lumens	1500 lumens	2000 lumens
WATTAGE	12W	18W	24W
CCT	(Easy Color SeleCCTor - 30K / 40K / 50K)		
CRI	90		
VOLTAGE	120V		
POWER FREQUENCY	50/60 Hz		
FINISH	White		
AMBIENT ENVIRONMENT	Damp location		

Compatible Junction Boxes:



Note: A 2-1/8" deep octagon junction box is recommended for through circuit wiring applications.

Ordering Information: Example: RL792-1000L-DIMTR-120-30K/40K/50K-90-WH

SERIES/APERTURE/LUMENS	DIMMING	VOLTAGE	CCT	CRI	FINISH
RL792-1000L - 7" aperture/1000 lumens	DIMTR - Triac	120 - 120V	30K/40K/50K - 3000K/4000K/5000K	90 - 90+ CRI	WH - White
RL992-1500L - 9" aperture/1500 lumens					BZ - Bronze
RL1192-2000L - 11" aperture/2000 lumens					BN - Brushed Nickel