

EM300S24DC Magnetic Driver

Description

Diffusion EM300S24DC is a magnetic low voltage, 24VDC dimmable LED driver.

Features

- Nema 3R for Indoor/Outdoor use
- Uses an assortment of dimmers including CFL/LED style
- Built in divider eliminating the need for a box
- Standard 3/8" KO
- Max load rated
- Mini breakers on the line and the low sides

See dimmer compatibility list

Specifications

- Input Voltage : 120V 60Hz
- Max Input Current at Full Load : 2.6A
- Output Voltage Without Load : 25.6 VDC
- Output Voltage : 23.5 VDC
- Max Wattage : 300W
- Max Output Current : 12.5A
- Efficiency : 90%
- Load Regulation : 0%
- Ripple : 0

