

Miniature Circuit Breaker ST200M

Ordering data characteristic C

| 1 pole | Box Qty | Weight each (kg) | Rated Current | Part number |
|--------|---------|------------------|---------------|-------------|
| | 10 | 0.115 | 0.5 A | ST201M-C0.5 |
| | | | 1.0 A | ST201M-C1 |
| | | | 1.6 A | ST201M-C1.6 |
| | | | 2.0 A | ST201M-C2 |
| | | | 3.0 A | ST201M-C3 |
| | | | 4.0 A | ST201M-C4 |
| | | | 5.0 A | ST201M-C5 |
| | | | 6.0 A | ST201M-C6 |
| | | | 7.0 A | ST201M-C7 |
| | | | 8.0 A | ST201M-C8 |
| | | | 10.0 A | ST201M-C10 |
| | | | 13.0 A | ST201M-C13 |
| | | | 15.0 A | ST201M-C15 |
| | | | 16.0 A | ST201M-C16 |
| | | | 20.0 A | ST201M-C20 |
| | | | 25.0 A | ST201M-C25 |
| | | | 30.0 A | ST201M-C30 |
| | | | 32.0 A | ST201M-C32 |
| | | | 35.0 A | ST201M-C35 |
| | | | 40.0 A | ST201M-C40 |
| | | | 50.0 A | ST201M-C50 |
| | | | 60.0 A | ST201M-C60 |
| | | | 63.0 A | ST201M-C63 |



| 1 pole + Neutral | Box Qty | Weight each (kg) | Rated Current | Part number |
|------------------|---------|------------------|---------------|---------------|
| | 5 | 0.230 | 0.5 A | ST201M-C0.5NA |
| | | | 1.0 A | ST201M-C1NA |
| | | | 1.6 A | ST201M-C1.6NA |
| | | | 2.0 A | ST201M-C2NA |
| | | | 3.0 A | ST201M-C3NA |
| | | | 4.0 A | ST201M-C4NA |
| | | | 5.0 A | ST201M-C5NA |
| | | | 6.0 A | ST201M-C6NA |
| | | | 7.0 A | ST201M-C7NA |
| | | | 8.0 A | ST201M-C8NA |
| | | | 10.0 A | ST201M-C10NA |
| | | | 13.0 A | ST201M-C13NA |
| | | | 15.0 A | ST201M-C15NA |
| | | | 16.0 A | ST201M-C16NA |
| | | | 20.0 A | ST201M-C20NA |
| | | | 25.0 A | ST201M-C25NA |
| | | | 30.0 A | ST201M-C30NA |
| | | | 32.0 A | ST201M-C32NA |
| | | | 35.0 A | ST201M-C35NA |
| | | | 40.0 A | ST201M-C40NA |
| | | | 50.0 A | ST201M-C50NA |
| | | | 60.0 A | ST201M-C60NA |
| | | | 63.0 A | ST201M-C63NA |



| 2 poles | Box Qty | Weight each (kg) | Rated Current | Part number |
|---------|---------|------------------|---------------|-------------|
| | 5 | 0.230 | 0.5 A | ST202M-C0.5 |
| | | | 1.0 A | ST202M-C1 |
| | | | 1.6 A | ST202M-C1.6 |
| | | | 2.0 A | ST202M-C2 |
| | | | 3.0 A | ST202M-C3 |
| | | | 4.0 A | ST202M-C4 |
| | | | 5.0 A | ST202M-C5 |
| | | | 6.0 A | ST202M-C6 |
| | | | 7.0 A | ST202M-C7 |
| | | | 8.0 A | ST202M-C8 |
| | | | 10.0 A | ST202M-C10 |
| | | | 13.0 A | ST202M-C13 |
| | | | 15.0 A | ST202M-C15 |
| | | | 16.0 A | ST202M-C16 |
| | | | 20.0 A | ST202M-C20 |
| | | | 25.0 A | ST202M-C25 |
| | | | 30.0 A | ST202M-C30 |
| | | | 32.0 A | ST202M-C32 |
| | | | 35.0 A | ST202M-C35 |
| | | | 40.0 A | ST202M-C40 |
| | | | 50.0 A | ST202M-C50 |
| | | | 60.0 A | ST202M-C60 |
| | | | 63.0 A | ST202M-C63 |



| 3 poles | Box Qty | Weight each (kg) | Rated Current | Part number |
|---------|---------|------------------|---------------|-------------|
| | 1 | 0.345 | 0.5 A | ST203M-C0.5 |
| | | | 1.0 A | ST203M-C1 |
| | | | 1.6 A | ST203M-C1.6 |
| | | | 2.0 A | ST203M-C2 |
| | | | 3.0 A | ST203M-C3 |
| | | | 4.0 A | ST203M-C4 |
| | | | 5.0 A | ST203M-C5 |
| | | | 6.0 A | ST203M-C6 |
| | | | 7.0 A | ST203M-C7 |
| | | | 8.0 A | ST203M-C8 |
| | | | 10.0 A | ST203M-C10 |
| | | | 13.0 A | ST203M-C13 |
| | | | 15.0 A | ST203M-C15 |
| | | | 16.0 A | ST203M-C16 |
| | | | 20.0 A | ST203M-C20 |
| | | | 25.0 A | ST203M-C25 |
| | | | 30.0 A | ST203M-C30 |
| | | | 32.0 A | ST203M-C32 |
| | | | 35.0 A | ST203M-C35 |
| | | | 40.0 A | ST203M-C40 |
| | | | 50.0 A | ST203M-C50 |
| | | | 60.0 A | ST203M-C60 |
| | | | 63.0 A | ST203M-C63 |

