



FM60-LED

6" LED FLUSHMOUNT - APOLLO SERIES

Product codes

FM60-0510-3K-WH : WHITE - 3K

FM60-0510-4K-WH : WHITE - 4K

AVAILABLE JUNE 2019

The APOLLO series is an affordable LED solution for any new construction or remodel applications. Easily installed on either a 3" or 4" junction box. Its low profile offers a stylish design with low energy costs.

Applications:

- Ceiling or surface mount
- Suitable for closets, storage areas, pantries & utility rooms

Features:

- 120V AC with driver on board technology
- Dimmable
- 50,000 Hour Life
- Available in White, 3K or 4K Color Temperature
- Certifications: ETL & Energy Star
- Units meet all UL 1598 Standards & ETL Labels
- Unit Mounting: Standard 3" or 4" electrical junction box
- 5 Year Warranty
- Damp Location rated

Données techniques

Diameter	5.75" (146.1 mm)
Height	1.00" (25.4 mm)
Color Temperature	3K / 4K
Light Output - Lumen	650LM
Operating Temperature	-20°C + 40°C
Dimmable	Y
CRI	80+
Voltage	120V
Watt	9W
Warranty (Years)	5
Bulb Life	50,000hrs
phase control	Forward Phase

