



SMART SWITCH, WI-FI, NICKEL

WWRL10NICCV2 | [radiant](#)

FEATURES & BENEFITS

Take comfort in the convenience of controlling your lights from any smart device to set the exact lighting you need - from anywhere.

The radiant Collection now offers smart switches and outlets with the ability to control lights and set scenes and schedules from any smart device - or just ask Alexa or Google to turn lights on for you. Combining classic design and advanced functionality with simple connection among existing smart home solutions, smart lighting sets the exact lighting you want - when and where you need it.

The radiant® Collection is a step up from standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.



- Control lights from smart phones and tablets with the Smart Lights app
- Schedule lights on/off automatically, group lights, and create Scenes
- Know your home is secure, even when you're away
- Just ask Amazon Alexa or the Google Assistant to turn lights on
- Out-of-the-box connectivity with OCF certification
- Installs easily in place of existing switch/dimmer
- Works in single pole or three way applications (works with any other 3-way switch)
- Requires neutral wire
- Locator light for finding switch the dark
- Available in white, light almond, and nickel colors
- Wall plate included
- Works with existing secure home Wi-Fi (WPA2)

SPECIFICATIONS

FCC ID: A3LCWAM210S

IC ID: 649E-CWAM210S

Prop65 Compliant

GENERAL INFO

Color: Nickel

Available Colors: White, Light Almond, Nickel

Connection Type: Certified IEEE 802.11™ b/g/n Wi-Fi® 2.4GHz radio

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

FCC Standard: Yes

UL Listing No: UL 916

UL Standard: Yes

CONSTRUCTION INFORMATION

Material 1: Polycarbonate Lexan

DIMENSIONS

Depth (US): 1.53"

Height (US): 4.17"

Width (US): 1.77"

Weight: 0.30 lbs.

TECHNICAL INFORMATION

Humidity: 0-90% relative humidity, non-condensing

Interoperability: OCF 1.3.1. / Works with Alexa / Works with Google Home Assistant

IP Rating: IP Native

Load: 120VAC / 60 Hz / 15A resistive | 1800W incandescent/halogen | 15A standard/electronic ballast | 5A LED | ½

HP motor

Operating Temperature (Celsius): 0°C to 43°C

Volts: 120V

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA