



S12210

6PAR20/LED/830/FL/120V
6W PAR20 LED; 3000K; 40 deg. beam spread; Medium base;
120V

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- Traditional lens
- Dimmable



S12210

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S12210	045923122101	120	6	65W	PAR20	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp	Color
6PAR20/LED/830/FL/120V	Dimmable	3 7/8"	2-1/2"	500	11000	3000	Soft White

CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	RoHS Compliant	UL Classification	Warranty
80	40	-20C (-4F) to a maximum of +45C (+113F)	24/6	Box	Yes	cULus - Wet Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

