

## Pole Mount Bracket



- SECC and SUS304 Stainless Steel Construction
- Designed for Reliability and Aesthetics

Technical Specifications		
Material	SECC and SUS304 Stainless Steel	
Color	White	
Dimensions (W x H x D)	130.40 mm x 170.0 mm x 45.0 mm (5.13 in. x 6.69 in. x 1.77 in.)	
Compatible Mast Diameter	ø80.0 mm to ø150.0 mm (ø3.15 in. to ø5.91 in.)	
Weight	0.85 kg (1.87 lb)	
Load Bearing Capacity	7.0 kg (15.40 lb)	
Operating Temperature	-40 °C to 60 °C (-40 °F to 140 °F)	
Humidity	0% to 90% RH	

Ordering Information		
Туре	Part Number	Description
Pole Mount	DH-PFA154	Pole Mount Bracket, White
Package Contents	1	Pole Mount Bracket
	3	M4 Screws
	1	Hex Wrench
	3	80 mm to 150 mm Metal Hoops

