

Quality Products. Service Excellence.

Type 4X Painted White Stainless Steel Wallmount Enclosure Eclipse

Series

Hinge Door with Handle



Panel Sold Separately









Application

- Designed to enclose electrical and/or electronic equipment and protect against harsh, industrial environments for wallmount applications.
- Impressive styling features like hidden hinges and attractive latching systems make the Eclipse a suitable addition to any high-tech equipment installation.
- A wide range of sizes and practical accessories make this product line a complete package.

Standards

- UL 508A Type 3R, 4, 4X and 12
- CSA Type 3R, 4, 4X and 12
- · Complies with
 - o NEMA 3R, 4, 4X, 12 and 13
 - o IEC 60529, IP 66

Construction

- Formed 14 gauge 304 stainless steel.
- · Continuously welded seams ground smooth.
- Door stiffeners are provided where required for increased strength and rigidity designed to also permit additional mounting options.
- Formed lip on enclosure to exclude flowing liquids and contaminants.
- Doors are secured with a 3 point Handle in 316 stainless with pad lockable feature.
- Doors may be easily removed for modifications and are interchangeable.
- · Seamless poured-in place gasket.
- Collar studs provided for mounting inner panel.
- Includes hardware kit with panel mounting nuts and sealing washers for wall mounting holes.
- Bonding stud provided on door and grounding stud installed in enclosure.
- Stainless steel hinge pins and hinges.

Finish

 Cover and enclosure are finished in recoatable smooth RAL 9003 White powder coating inside and out.

Accessories

- Additional Inner Panels
- Swing Frame
- Eclipse DIN Rails
- Mounting Foot Kit
- Drip Shield Kit
- Replacement Hinge Pins
- Lighting

- Swing Panel
- Eclipse DIN Rail Mounting Kit
- Door Stop Kit
- Rear Hole Plugs
- Type 12/4, 4X Handle Kits
- Climate Control
- · General Accessories

New and improved PDF part drawing files with more detail now available.

Click part number in table below to access PDF, DXF, and STEP files.

	Enclosure			Optional Inner Panel		
Part No.	Н	W	D	Part No.	Н	W
EN4SD24248SSWH	24.00	24.00	8.00	EP2424	22.20	22.20
EN4SD30248SSWH	30.00	24.00	8.00	EP3024	28.20	22.20
EN4SD242010SSWH	24.00	20.00	10.00	EP2420	22.20	18.20
EN4SD242412SSWH	24.00	24.00	12.00	EP2424	22.20	22.20
EN4SD363012SSWH	36.00	30.00	12.00	EP3630	34.20	28.20
EN4SD363612SSWH	36.00	36.00	12.00	EP3636	34.20	34.20
EN4SD423612SSWH	42.00	36.00	12.00	EP4236	40.20	34.20
EN4SD483612SSWH	48.00	36.00	12.00	EP4836	46.20	34.20
EN4SD483616SSWH	48.00	36.00	16.00	EP4836	46.20	34.20
EN4SD603612SSWH	60.00	36.00	12.00	EP6036	58.20	34.20

Alternative inner panel options also available.

Data subject to change without notice

© 2021. Hammond Manufacturing Ltd. All rights reserved.