



## Block and Tackle Spliced to Cat. No. 268 Block



Light, galvanized-steel shell blocks are fitted with snubbing hooks to hold the load. Sheaves are strong yet lightweight aluminum alloy with all-bronze bushings. Available with standard snap hooks or guarded snap hooks (with snap hook nose lengthened to extend over the latch or keeper).

### Specifications

<b>Overall Length:</b>	12.096	<b>Overall Height:</b>	5.189
<b>Overall Width:</b>	4.5	<b>Material:</b>	Galvanized-Steel Shell Blocks, Aluminum Alloy Bushings, Nylon Rope
<b>Hook Type:</b>	Standard	<b>Rope Material:</b>	Nylon
<b>Rope Diameter:</b>	3/8" (9.53 mm)	<b>Rope Length:</b>	25'
<b>Maximum Safe Load:</b>	750 lb (340 kg)	<b>Included:</b>	268 Block
<b>Weight:</b>	2.8 lb (1.3 kg)		