



Cutting Crimping Pliers, Insulated, 9-Inch



These Klein Tools 9-Inch Insulated Side-Cutting Crimping Pliers offer protection against electric shock up to 1000 volts. The pliers are individually tested to exceed the IEC 60900 and ASTM F1505 standards, for insulated tools, and clearly marked with the official 1000-volt rating symbol. The pliers offer maximum strength with their forged-steel construction and a crimping die helps provide increased leverage.

Specifications

Type:	High-Leverage Connector Crimping Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wires
Special Features:	Integral Guards Help Prevent Hand Contact With Conductive Parts	Overall Length:	9.68" (24.6 cm)
Material:	Induction Hardened Steel	Nose Type:	New England
Jaw Length:	1.594" (4.1 cm)	Jaw Width:	1.313" (3.3 cm)
Jaw Thickness:	0.625" (1.6 cm)	Jaw Capacity:	1.43" (3.6 cm)
Knife Length:	0.781" (2 cm)	Cut Style:	Side-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer	Insulated:	Yes
Standard:	IEC 60900 and ASTM F1505	Weight:	1.3 lb (0.6 kg)