



Diagonal Cutting Pliers, Insulated, High-Leverage, Angled Head, 8-Inch



These Insulated Diagonal-Cutting pliers feature two layers of insulation to protect against electric shock. Clearly marked with the official 1000V symbol, these pliers meet or exceed ASTM F1505-16 and IEC 60900:2018 standards for insulated tools. The head is angled to get into confined spaces. The high-leverage design provides 36-percent greater cutting power than other plier designs.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	8.25" (21 cm)
Material:	Induction Hardened Steel	Nose Type:	Angled
Jaw Length:	0.813" (2.1 cm)	Jaw Width:	1.188" (3 cm)
Jaw Thickness:	0.813" (2.1 cm)	Jaw Capacity:	1.07" (2.7 cm)
Cutting Knives:	Standard	Cut Style:	Diagonal-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer	Handle Length:	6" (15.2 cm)
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight:	11.2 oz (318 g)		