



Diagonal Cutting Pliers, Insulated, Heavy-Duty, Angled Head, 8-Inch



These Insulated Heavy-Duty Diagonal-Cutting Pliers have durable molded insulation that is flame retardant, impact resistant and clearly marked with 1000-volt rating. The knives are heavy duty induction hardened steel that can cut ACSR, screws, nails, and most hardened wire. The high-leverage design paired with an angled head allows for increased leverage and the ability to work in confined areas.

Specifications

Type:	Diagonal Cutting Pliers	Application:	ACSR, Screws, Nails and Most Hardened Wire
Special Features:	Flame Retardant and Impact Resistant Handle	Overall Length:	8.25" (21 cm)
Material:	Induction Hardened Steel	Nose Type:	Angled
Jaw Length:	0.813" (2.1 cm)	Jaw Width:	1.188" (3 cm)
Jaw Thickness:	0.813" (2.1 cm)	Jaw Capacity:	1.15" (2.9 cm)
Cutting Knives:	Standard	Cut Style:	Diagonal-Cutting
Joint Type:	Hot-Riveted	Handle Color:	Orange
Handle Finish:	2-Layer	Handle Length:	6.75" (17.2 cm)
Insulated:	Yes	Standard:	IEC 60900 and ASTM F1505
Weight:	11.2 oz (318 g)		