



Journeyman™ Pliers Connector Crimp Side Cut 9-Inch



These Klein Tools Journeyman Pliers Connector Crimp Side Cut, have a high-leverage design, including the crimping die being placed behind the hinge. They are induction hardened and have a hot-riveted joint for smooth and powerful action without handle wobble. They also have cross-hatched knurled jaws and "handform" handles for better all around grip.

Specifications

Type:	High Leverage Side Cutting/Connector Crimping Pliers	Application:	Crimps Noninsulated Connectors, Lugs, and Terminals
Overall Length:	9.55" (24.3 cm)	Material:	Steel
Nose Type:	New England	Jaw Length:	1.594" (4.1 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.625" (1.6 cm)
Jaw Capacity:	1.44" (3.7 cm)	Knife Length:	0.781" (2 cm)
Cut Style:	Flush	Handle Color:	Yellow/Black
Handle Finish:	Journeyman	Handle Length:	6.75" (17.2 cm)
Insulated:	No	Tether Capable:	No
Weight:	1.1 lb (0.5 kg)		