



Lineman's Pliers, Crimping, 9-Inch



These Lineman's Pliers feature a built-in crimper for non-insulated connectors. Heavy-duty cutting knives cut ACSR, screws, nails and most hardened wire. The high-leverage design provides 46-Percent more cutting power. The dual-material Journeyman handles are more comfortable and durable than other handles.

Specifications

Type:	Heavy Duty High Leverage Side Cutting/Crimping Pliers	Application:	ACSR, Screws, Nails, Most Hardened Wire; Crimps Noninsulated Connectors, Lugs and Terminals
Overall Length:	9.55" (24.3 cm)	Material:	Steel
Nose Type:	New England	Jaw Length:	1.594" (4.1 cm)
Jaw Width:	1.25" (3.2 cm)	Jaw Thickness:	0.625" (1.6 cm)
Jaw Capacity:	1.43" (3.6 cm)	Knife Length:	0.781" (2 cm)
Handle Color:	Light Blue/Black	Handle Finish:	Journeyman
Handle Length:	7.375" (18.7 cm)	Insulated:	No
Tether Capable:	No	Weight:	1.1 lb (0.5 kg)