



Journeyman Universal Combination Pliers



These 8-Inch Universal High-Leverage Combination Pliers feature a crimping die behind the hinge for superior leverage while crimping non-insulated connectors, lugs and terminals and a high-leverage design, with the rivet closer to the cutting edge for 40% greater cutting and gripping power than other pliers designs. The universal tapered head-design allows for greater access in confined spaces. Klein's trademark dual-material Journeyman handles feature a soft outer surface for comfort and a hard inner material for toughness and durability.

Specifications

Type:	Journeyman Combination Pliers	Application:	Noninsulated Connectors, Lugs, and Terminals
Overall Length:	8.78" (22.3 cm)	Material:	Steel
Nose Type:	Universal	Jaw Length:	1.781" (4.5 cm)
Jaw Width:	1.031" (2.6 cm)	Jaw Thickness:	0.53" (1.4 cm)
Jaw Capacity:	2.125" (0.2 cm)	Knife Length:	0.75" (1.9 cm)
Handle Color:	Dark Blue/Black	Handle Finish:	Journeyman
Handle Length:	5.75" (14.6 cm)	Insulated:	No
Tether Capable:	No	Weight:	13.1 oz (372 g)