



# LED Tape Kit

STANDARD's LED Tape kits are designed to add ambiance and character to any setting. Delivering even, brilliant light, the colour changing RGB, cool white and warm white colours can be used in a multitude of applications, both indoor and outdoor, ranging from under cabinets to cove and perimeter applications.



Order code	Description	Watts per reel (W)		Volts (VDC)	Colour	Length		Life L70 (hrs)	Lumen output (lm)		Number of LED chips (per ft.) (per m)	Dimming capability (Yes/No)	Case qty (master)
		(per ft.)	(per m)			(ft.)	(m)		(per ft.)	(per m)			

## LED Tape Kits

61953	LED/TAPE/16.4'/5050/RGB KIT/12V/50M/STD	5.4	1.6	12	RGB	16.4	5	50 000	-	-	9	30	Yes	20
61954	LED/TAPE/16.4'/5050/WW KIT/12V/50M/STD	5.6	1.7	12	Warm white	16.4	5	50 000	145	175.6	9	30	No	20
61955	LED/TAPE/16.4'/5050/CW KIT/12V/50M/STD	5.6	1.7	12	Cool white	16.4	5	50 000	145	175.6	9	30	No	20

## Plug-in Drivers - Non-dimmable

62265	LED/TAPE/36W/12V/WW+CW/PS/ND/STD	-	-	12	White	6.56	2	-	-	-	-	-	-	50
62266	LED/TAPE/36W/12V/RGB/PS/ND/STD	-	-	12	White	6.56	2	-	-	-	-	-	-	50

## Accessories

Order code	Description	Type	Case qty
			(inner/master)
61956	LED/TAPE/RGB/CONNECTOR/STD	RGB Connector	10/50
61957	LED/TAPE/WW+CW/CONNECTOR/STD	Connector	10/100
62017	LED/10PCS TAPE LIGHT 12V MOUNTING CLIPS	Mounting clips	1/100



## Included in the box

- 1 tape light 16.4' (5 m)
- 1 plug-in driver
- 1 RGB remote control (for RGB kit only)



Lumen values are derived from photometric testing.  
For a complete list of compatible dimmers, please visit [www.standardpro.com](http://www.standardpro.com)  
Note: To avoid decreases in light levels, avoid connecting more than 16.4' (5 m) at a time