

Project Name

Location

Prepared By



Notes

General

Status	Active
Finish	Black
Wattage	10
Style	Utility
CCT (Kelvin)	3000
Color Temperature	Warm White
Length (in.)	2.38
Width (in.)	5
Height (in.)	6.75
Extension (in.)	3.41

Specifications

Technology	LED
CRI	90
Lumen Output	750
Rated Hours	50000
Voltage	120V/277V
Dimmable	Non-Dimmable
Weight (lb.)	1.72
Fixture Material	Die Cast Aluminum
Recommended Dimmer	N/A
Fixture Type	Sconce

Compliance

UL Application	Outdoor
Energy Star	Yes
ES Unique ID	ESID-2336404
CEC Status	California T24 Compliant
CA Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Installation Notes	Mounts Up and Down
Warranty	5 Year Limited