

Project Name

Location

Prepared By



**Notes**

**General**

|                   |            |
|-------------------|------------|
| Status            | Active     |
| Finish            | White      |
| Wattage           | 10         |
| Style             | Utility    |
| CCT (Kelvin)      | 3000       |
| Color Temperature | Warm White |
| Length (in.)      | 2.38       |
| Width (in.)       | 5          |
| Height (in.)      | 6.75       |
| Extension (in.)   | 3.41       |

**Specifications**

|                    |                   |
|--------------------|-------------------|
| Technology         | LED               |
| CRI                | 90                |
| Lumen Output       | 750               |
| Rated Hours        | 50000             |
| Voltage            | 120V/277V         |
| Dimmable           | Non-Dimmable      |
| Weight (lb.)       | 1.72              |
| Fixture Material   | Die Cast Aluminum |
| Recommended Dimmer | N/A               |
| Fixture Type       | Sconce            |

**Compliance**

|                |                          |
|----------------|--------------------------|
| UL Application | Outdoor                  |
| Energy Star    | Yes                      |
| ES Unique ID   | ESID-2336404             |
| CEC Status     | California T24 Compliant |
| CA Prop 65     | Lead                     |
| RoHS Compliant | Yes                      |

**Additional Information**

|                    |                    |
|--------------------|--------------------|
| Installation Notes | Mounts Up and Down |
| Warranty           | 5 Year Limited     |