

Project Name

Location

Prepared By



## NUVO 65-582

2X4 LED BACKLIT FLAT PANEL

Notes

### General

Status	Active
Fixture Type	Flat Panel
Finish	White
Wattage	50
Lumen Output	5250L/5500L/5500L
CCT (Kelvin)	3500K/4000K/5000K

### Specifications

Technology	LED
CRI	80+
Voltage	100V-347V
Rated Hours	50000
Operating Temperature	-17C (1F) to a maximum of +45C (+113F)
Dimmable	0-10V Dimming Only
Photocell	No Photocell
Weight (lb.)	9.04

### Dimensions

Height (in.)	1.5
Width (in.)	23.75
Length (in.)	47.72

### Compliance

Safety Listing	cETLus
Location Rating	Damp
UL Application	Ceiling
Energy Star	No
DLC Approved	Yes
DLC ID	PLQG0GTV7QRN
CEC Status	Lawful for sale in California
RoHS Compliant	Yes

### Additional Information

Warranty	5 Year Limited
----------	----------------