


## Straight Non-Metallic Connectors



For use with non-metallic liquid-tight conduit, type B only. Produced from UV rated plastic for long outdoor life.

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	TRADE SIZE	KO SIZE	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
NMLT38	54380	3/8	1/2	25	100	1.545	.535	1.410
NMLT50	54500	1/2	1/2	25	100	1.545	.535	1.410
NMLT75	54750	3/4	3/4	10	50	1.600	.550	1.595
NMLT100	54100	1	1	5	25	1.975	.670	1.930
NMLT125	04223	1-1/4	1-1/4	5	25	2.293	.645	2.428
NMLT150	04222	1-1/2	1-1/2	2	10	2.175	.660	2.700
NMLT200	04221	2	2	2	10	2.400	.670	3.360

Add suffix "BL" to Catalog # when ordering in black, for example NMLT38BL.



### INSTALLATION INSTRUCTIONS

Arlington's reusable Liquid-Tight Fittings may be secured to conduit while fully assembled because of our no-spin ferrule. Simply loosen nut, and screw onto conduit. A positive liquid-tight seal is provided by our pressure sensitive internal gland when the nut is tightened. A liquid-tight seal is also assured between the fitting and box by a sealing ring.