L¹ legrand[®]


Switches Extra Heavy-Duty Lighted 15, 20 & 30A; 120, 277 & 120/277VAC


Pass & Seymour

PS15AC1-SL, PS15AC3-SL, PS20AC1-SL, PS20AC3-SL, PS15AC1-PL, PS15AC3-PL, PS20AC1-PL, PS20AC2-PL, PS20AC3-PL, PS30AC1-PL, PS30AC2-PL, PS30AC3-PL

Commercial quality with added convenience and safety.

hese extra-rugged switches offer all the solid construction, excellent operating feel, and easy installation features of our Extra Heavy-Duty Switches. They add a choice of two light options. Lighted toggle switches are illuminated when off for easy location in the dark. Pilot lighted switches are illuminated when on for easy monitoring.





SF102R2 — Updated April 2006 — For latest specs visit www.legrand.us/passandseymour



Pass & Seymour

La legrand[®] Switches Extra Heavy-Duty Lighted 15, 20 & 30A; 120, 277 & 120/277VAC

Ordering Information

Catalog Number			Rating		
Single Pole	Double Pole	Three-Way	Α.	VAC	Color
Lighted Toggle Switches (Lighted when OFF) Back & Side Wire					
PS15AC1-CSL		PS15AC3-CSL	15	120/277	Clear
PS15AC1-ISL		PS15AC3-ISL	15	120/277	lvory
PS15AC1-WSL		PS15AC3-WSL	15	120/277	White
PS20AC1-CSL		PS20AC3-CSL	20	120/277	Clear
PS20AC1-ISL		PS20AC3-ISL	20	120/277	lvory
PS20AC1-WSL		PS20AC3-WSL	20	120/277	White
PS20AC1-LASL		PS20AC3-LASL	20	120/277	Light Almond
Pilot Lighted Switches (Lighted when ON) Back & Side Wire					
			1		
PS15AC1-CPL		PS15AC3-CPL	15	120	Clear
PS15AC1-CPL PS15AC1-RPL		PS15AC3-CPL PS15AC3-RPL	15 15	120 120	Clear Red
					0.00
PS15AC1-RPL			15	120	Red
PS15AC1-RPL PS20AC1-CPL		PS15AC3-RPL	15 20	120 120	Red Clear
PS15AC1-RPL PS20AC1-CPL PS20AC1-CPL7		PS15AC3-RPL PS20AC3-CPL7	15 20 20	120 120 277	Red Clear Clear
PS15AC1-RPL PS20AC1-CPL PS20AC1-CPL7 PS20AC1-RPL	PS20AC2-CPL	PS15AC3-RPL PS20AC3-CPL7 PS20AC3-RPL	15 20 20 20	120 120 277 120	Red Clear Clear Red
PS15AC1-RPL PS20AC1-CPL PS20AC1-CPL7 PS20AC1-RPL	PS20AC2-CPL PS20AC2-RPL	PS15AC3-RPL PS20AC3-CPL7 PS20AC3-RPL	15 20 20 20 20 20	120 120 277 120 277	Red Clear Clear Red Red
PS15AC1-RPL PS20AC1-CPL PS20AC1-CPL7 PS20AC1-RPL		PS15AC3-RPL PS20AC3-CPL7 PS20AC3-RPL	15 20 20 20 20 20 20	120 120 277 120 277 120/277	Red Clear Clear Red Red Clear

For more information on these and other P&S products refer to our Catalog or visit our web site.

Switches Extra Heavy-Duty Lighted 15, 20 & 30A; 120, 277 & 120/277VAC



Technical Specifications

3rd Party Compliance

UL Listed, File Number E140597, Standard UL20, General Use Snap Switches. Federal Specification WS896. cULus Listed, File Number LR17446, Standard CSA-C22.2 No. 111, General Use Snap Switches. Conforms to NEMA WD-1 and WD-6.

Performance	
Electrical Dielectric Withstand Voltage Maximum Working Voltage Overload Temperature Rise Maximum Continuous Current Endurance	1500V Minimum 277VAC Minimum 4.8 times rated current for 100 cycles 30°C maximum at rated current 277VAC 50,000 cycles minimum, resistive, inductive, tungsten filament lamp load (Fed Spec)
Mechanical Terminal Accommodations	#14 AWG – #10 AWG
Environmental Flammability Operating Temperature	UL94 V2 Maximum continuous +115°C, minimum -40°C

Materials

Back Body Glass-Reinforced Nylon Front Body Nylon Toggle Thermoplastic Polycarbonate Terminals Brass **Terminal Screws Tri-Drive Brass** Strap Nickel-Plated Brass **Pressure Plate** Brass Contacts Silver Cadmium Oxide

Blue


Red

Green


15 Amp Cover 20 Amp Cover 30 Amp Cover

Warranty

1 Year



Dimensions for 15 & 20 Amp Lighted and Pilot Lighted



Dimensions for 30 Amp Lighted and Pilot Lighted

Spring Arm Bumper Spring Ground Terminal Ground Screw Auto-Ground Clip Illuminating Lamp Brass Rubber Zinc-Plated Steel Brass Tri-Drive Zinc-Plated Steel Nickel-Plated Brass Neon