

Project Name

Location

Prepared By



SATCO S11417

9.5A19/LED/850/120V/D/4PK

Notes

General

Status	Active
Watts	9.5
Incandescent Equivalent	60
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	80
Lumens	800
Beam Spread	230
Dimmable	Yes Dimmable
Hours Rated	15000

Physical

MOL	4.17
MOD	2.38

Additional Information

Enclosure Rating	Enclosed Rated Lamp
------------------	---------------------

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Non-Compliant
RoHS Compliant	Yes