

Project Name

Location

Prepared By



## SATCO S11422

15.5A19/LED/827/120V/D/4PK

Notes

### General

Status	Active
Watts	15.5
Incandescent Equivalent	100
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	1600
Beam Spread	230
Dimmable	Yes Dimmable
Hours Rated	15000

### Physical

MOL	4.57
MOD	2.38

### Additional Information

Enclosure Rating	Enclosed Rated Lamp
------------------	---------------------

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Non-Compliant
RoHS Compliant	Yes