



Wire Strippers/Cutters

Includes core features plus:

- Narrow nose fits into tight places
- Cat. Nos. 1011 and 1011M strip six standard wire sizes without nicking wire
- Cat. No. 11048 strips two wires in a single motion
- Do not use for cutting steel wire or screws





| Cat. No. | Strips and Cuts | Overall Length | Handle Color | Weight |
|----------|---|-------------------|--------------|-------------------|
| 11045 | 10-18 AWG Solid (6.0-1.0 mm²) | 6.25" (158.8 mm) | Yellow | 0.27 lb (0.12 kg) |
| 11046 | 16-26 AWG Stranded (1.5-0.14 mm²) | 6.25" (158.8 mm) | Red | 0.27 lb (0.12 kg) |
| 11047 | 22-30 AWG Solid (0.35-0.05 mm²) | 6.25" (158.8 mm) | Yellow | 0.27 lb (0.12 kg) |
| 11049 | 8-16 AWG Stranded (6 mm ² -1.0 mm ²) | 6.25" (158.8 mm) | Red | 0.27 lb (0.12 kg) |
| 11048 | 10, 12, 14 AWG Solid (4.0 mm², 2.5 mm², 1.5 mm²) | 6.25" (158.8 mm) | Yellow | 0.27 lb (0.12 kg) |
| 1011 | 10-20 AWG Solid (6.0-0.50 mm²); 12-22 AWG Stranded (4.0-0.35 mm²) | 6.125" (155.6 mm) | Blue | 0.23 lb (0.10 kg) |
| 1011M | 0.15 to 4.0 mm ² Stranded Wire | 6.125" (155.6 mm) | Blue | 0.23 lb (0.10 kg) |

Adjustable Wire Stripper/Cutters

- Cuts and strips solid and stranded wire
- Handy, light, compact tools for stripping insulation
- Adjustable dial for wire size adjustment prevents nicked wire (Cat. No. 74007)
- Adjustable slide stop with set screw for repeated stripping work (Cat. No. 1003, 1004)
- Convenient hole for looping or bending wire (Cat. No. 1003, 1004)
- Black-oxide finish with plastic-dipped handles



| Cat. No. | Strips and Cuts | Hold-Open Spring | Overall Length | Handle Color | Weight |
|----------|--|------------------|-------------------|--------------|-------------------|
| 74007 | 12-24 AWG Solid and Stranded (4.0-0.25 mm²) | Yes | 5.125" (130.2 mm) | Yellow | 0.15 lb (0.07 kg) |
| 1004 | 12-26 AWG Solid and Stranded (4.0- 0.14 mm²) | Yes | 5" (127.0 mm) | Yellow | 0.18 lb (0.08 kg) |
| 1003 | 12-26 AWG Solid and Stranded (4.0- 0.14 mm²) | No | 5" (127.0 mm) | Yellow | 0.14 lb (0.06 kg) |

