




Fish Tapes


Fiberglass Fish Tapes

Includes core fish tape features plus:

- Designed for flexibility and easy navigation through conduit runs
- Non-conductive, fiberglass fish tape slides easily over existing wires and through multiple bends
- Durable 7" (178 mm) leader helps push through crowded conduit
- The lightweight and strong fiberglass composite tape resists harsh elements and is strength rated up to 500 pulling pounds
- Repair kit (Cat. No. 56115) available to replace tips
- Replacement metal eyelets (Cat. No. 56116) and spiral steel leaders (Cat. No. 56120) available



7" spiral steel leader



1' permanent laser etched descending increments.



56010

Cat. No.	Tape Size	Diameter	Weight
56009	50' x 3/16" (15.2 m x 4.8 mm)	13" (330.2 mm)	2.8 lb (1.3 kg)
56010	100' x 3/16" (30.5 m x 4.8 mm)	13" (330.2 mm)	3.5 lb (1.6 kg)
56014	200' x 3/16" (60.96 m x 4.8 mm)	17" (431.8 mm)	6.2 lb (2.8 kg)

Steel Fish Tapes

Includes core features plus:

- Stainless Steel fish tape is corrosion resistant extending the life of the tool (Cat. Nos. 56007, 56008)
- High strength spring steel fish tapes are stiff for long runs and are great for heavy-duty wire pulls
- Full grip style handle gives you a firm, steady grip as you pull tape from the case
- Tempered, high quality tape keeps its stability as it glides between surfaces for effective pushing and pulling of wire under carpets, through insulated walls and over suspended ceilings
- 25' length with no snag tip is perfect for short wire runs associated with light commercial, residential and voice-data-video-audio installations (Cat. No. 56005)

Cat. No.	Tape Size	Diameter	Weight
1/8" Wide Steel Fish Tapes			
56007	125' x 1/8" x 0.062" (38.1 m x 3.2 mm x 1.57 mm)	13" (330.2 mm)	4.7 lb (2.1 kg)
56008	240' x 1/8" x 0.062" (73.2 m x 3.2 mm x 1.57 mm)	13" (330.2 mm)	7.5 lb (3.4 kg)
56000	25' x 1/8" x 0.045" (7.6 m x 3.2 mm x 1.14 mm)	7" (177.8 mm)	1.0 lb (0.5 kg)
56001	50' x 1/8" x 0.045" (15.2 m x 3.2 mm x 1.14 mm)	7" (177.8 mm)	1.3 lb (0.6 kg)
56002	65' x 1/8" x 0.062" (19.8 m x 3.2 mm x 1.57 mm)	9" (228.6 mm)	2.6 lb (1.2 kg)
56003	125' x 1/8" x 0.062" (38.1 m x 3.2 mm x 1.57 mm)	13" (330.2 mm)	4.7 lb (2.1 kg)
56004	240' x 1/8" x 0.062" (73.2 m x 3.2 mm x 1.57 mm)	13" (330.2 mm)	7.5 lb (3.4 kg)
1/4" Wide Steel Fish Tapes			
56005	25' x 1/4" x 0.030" (7.6 m x 6.4 mm x 0.76mm)	7" (177.8 mm)	1.1 lb (0.5 kg)
56006	100' x 1/4" x 0.062" (30.5 m x 6.4 mm x 1.57 mm)	13" (330.2 mm)	6.8 lb (3.1 kg)



56001

Tip side profile



No snag plastic tip (Cat. No. 56005)



1' permanent laser etched descending increments.



Spiral Steel Fish Tapes

Includes core fish tape features plus:

- Designed for super flexibility and easy navigation through conduit runs
- Slides easily over existing wires and through multiple bends
- The durable spiral steel tape construction yields a maximum pulling force of up to 250 lbs.
- Replacement metal eyelets (Cat. No. 56116) and spiral steel leaders (Cat. No. 56120) available



7" spiral steel leader



56013

Cat. No.	Tape Size	Diameter	Weight
56013	50' x 3/16" (15.2 m x 4.8 mm)	13" (330.2 mm)	5.1 lb (2.3 kg)

See page 297 for additional information on warnings.



WARNING: Never remove screws while fish tape is coiled inside reel.