# Cable and Bolt Cutters



**Cable Cutters** 

### **Hot-riveted joint**

ensures smooth action and no handle wobble

### Beveled jaw tips

provide proper mating and shearing action, which protects leading jaw edges



## **High-Leverage Cable Cutters**

#### Includes core cable cutter features plus:

- High-leverage design for exceptional cutting capability
- Precision, one-hand shearing action
- Cable-gripping shear-type jaws
- Perfect for working in confined spaces

Refer to the insulated section for insulated cable cutters

• Fits in most tool pouches/belts



63050





Plastic-Dipped

J0URNEYMAN™ Dual-Material

Cat. No.	Cutting Capacity	Handle Color	Handle Finish	Overall Length	Weight
63050	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	Red	Plastic-Dipped	9.39" (238.5 mm)	0.90 lb (0.41 kg)
J63050	4/0 Aluminum, 2/0 Soft Copper, 100-Pair 24 AWG Communications Cable	Red/Black	Journeyman	9.563" (242.9 mm)	0.98 lb (0.44 kg)

### **Cable Cutters - Coaxial**

#### Includes core cable cutter features plus:

- Cable-gripping jaws quickly score jacket and insulation, and easily cut through copper inner conductor
- Blades cleanly cut aluminum and copper coaxial cable without compression and frayed ends
- Forged body with heat-treated and precision-ground steel blade withstands frequent cutting
- Hot-riveted design requires no adjustment while maintaining a smooth, precise operation
- Compact, lightweight design fits perfectly in any professional's tool pouch
- When cutting drop wire with an inner steel conductor, we recommend our 2000 Series cutting pliers



63030

Cat. No.	Cutting Capacity	Handle Color	Handle Finish	Overall Length	Weight
63028	3/4" (19.1 mm)	Yellow	Plastic-Dipped	8.25" (209.6 mm)	0.80 lb (0.36 kg)
63030	1" (25.4 mm)	Blue	Plastic-Dipped	8.25" (209.6 mm)	0.83 lb (0.38 kg)

See page 297 for additional information on warnings.





# **Cable Cutters**

### **Compact Cable Cutter**

#### Includes core cable cutter features plus:

- Precise, one-hand shearing action cuts 24 AWG copper, aluminum multi-strand cable and wire, and 100-pair telephone cable
- Special shear angle cuts cleanly without compression to cable geometry for telecom cable work
- Heat-treated, high-carbon steel shearing edges for long life
- Forged body with 3/8" (10 mm) case-hardened rivet



<b>∆WARNING:</b>	Do	NOT	cut steel	or	ACSR.

Cat. No.	Cutting Capacity	Handle Color	Handle Finish	Overall Length	Weight
63055	24 AWG Copper, Aluminum Multi-Strand Cable and Wire, and 100-Pair Telephone Cable	Red	Plastic-Dipped	8" (203.2 mm)	0.65 lb (0.29 kg)

## **All-Purpose Shears and BX Cutter**

#### Includes core cable cutter features plus:

- Handle cavity is designed to restore BX cable to original shape after cutting
- Stripping notch for added convenience
- High-leverage, shear-type design for one-hand operation
- Lighweight and compact



1104

**MARNING:** Do NOT cut steel or ACSR.

Cat. No.	Cutting Capacity	Handle Color	Handle Finish	Overall Length	Weight
1104	Cuts BX Cable, Sheet Metal, Steel Strapping and Bundling Wire	Red	Plastic Dipped	7.625" (193.7 mm)	0.60 lb (0.27 kg)

# **Heavy-Duty Cable Shears**

- · Cuts ACSR, steel, and most hardened wire
- Heavy-duty, tempered steel blades
- Blades grip cable and cut easily at center of jaws
- Lock keeps handles closed for easy storage
- · Comfortable, plastic-coated handles for steady grip
- Hardened steel, precision cutting blades for long service life
- Unique triangular jaws cleanly cut cable without compression or frayed ends



63016

Cat. No.	Cutting Capacity	Handle Color	Handle Finish	Overall Length	Weight
63016	Up to 1/4"(6.4 mm) Copper and Mild Steel Strands, up to 3/16" (4.8 mm) Aircraft Cable, Wire Rope, Aluminum and Copper Rods, up to 5/32"(4 mm) for Steel and Iron Rods	Blue	Plastic-Dipped	7.5" (190.5 mm)	0.65 lb (0.29 kg)

### **Multi-Cable Cutter**

- Hardened steel precision-ground cutting blades for long life
- · Copper curved cutter cleanly cuts round copper cable without compression or frayed ends
- Double-dipped grips for comfort
- Coil spring provides fast self-opening action
- Holes for looping and bending wire
- Convenient lock for storage also prevents accidental locking and loosening over time



63020

Cat. No.	Cutting Capacity	Screw Shearing	Handle Color	Overall Length	Weight
63020	Up to 12 AWG Solid and Stranded Copper Wire, Up to 0.032" (.081 mm) Diameter Stainless Steel, Up to 1/2" (12.7 mm) Multi-conductor Cable, Coaxial Cable RG-6 Quad, RG-59 and RG-62	6-32 & 8-32	Red	7" (177.8 mm)	0.44 lb (0.20 kg)



# **Cable Cutters**

## **Utility Cable and Rope Cutters**

- Forged steel with black-oxide finish for long life
- Shear-type hook jaws grab and hold cable while shear-cutting action makes clean cuts
- Beveled tips for positive mating
- Hinge bolt with pin-set nut for proper blade tension
- Cat. No. 63035SC cuts wire up to 9/32" (7 mm) and Stoffel® container seals
- Cat. No. 63035 is not designed to cut steel or ACSR



63035SC

Cat. No.	Cutting Capacity	Handle Color	Overall Length	Weight
63035	MCM Cable 350 Copper, 350 Aluminum	Red	16.25" (412.8 mm)	1.7 lb (0.8 kg)
63035SC	9/32" (7.1 mm) Wire Rope and Cables	Red	18" (457.2 mm)	2.0 lb (0.9 kg)

Stoffel® is a registered trademark of Stoffel Seals Corporation.

### **Standard and Communication Cable Cutters**



Cat. No.	Soft Cable Maximum Capacity	MCM Cable Maximum Capacity	Replacement Blade	Overall Length	Weight
63041	1-3/8" (34.9 mm) Diameter	MCM 500 Copper, 750 Aluminum	63081	25.5" (647.7 mm)	5.3 lb (2.4 kg)
63041TH	1-3/8" (34.9 mm) Diameter	MCM 500 Copper, 750 Aluminum	63081	25.5" (647.7 mm)	5.3 lb (2.4 kg)
63045	1-3/4" (44.5 mm) Diameter	1000 Copper, 1200 Aluminum	63090	32" (812.8 mm)	8.0 lb (3.6 kg)
63047	Up to 2-1/4" (57.2 mm) Diameter	900-Pair Soft Copper and Aluminum	63110	37" (939.8 mm)	8.6 lb (3.9 kg)