

Multi-Bit Screwdrivers/Nut Drivers

10-in-1 Folding Screwdriver/Nut Driver

10-FOLD™



32535

- Conveniently folds up for easy storage or to fit into your pocket
- Each driver arm contains four interchangeable bit styles and two nut drivers
- Unfold each driver arm up to a full 180° for straight on driving power, or at 90° for extra leverage on stubborn fasteners
- Quick release button easily unlocks a fully extended driver arm

32534
Schrader®



32535
Standard



32536
TORX®



32537
Tamperproof TORX®



32538
Standard Hex



32539
Metric Hex



Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	TORX® Bits	Other Bits	Handle Color	Weight
32534	5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	—	—	Schrader® Valve Insertion/ Core Removal	Blue	0.37 lb (0.17 kg)
32535	5/16", 1/4"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	#1, #2	—	T10, T15	—	Black	0.37 lb (0.17 kg)
32536	5/16", 1/4"	—	—	—	—	T6, T7, T8, T10, T15, T20, T25, T27	—	Green	0.37 lb (0.17 kg)
32537	5/16", 1/4"	—	—	—	—	T7, T8, T9, T10, T15, T20, T25, T27	—	Green	0.37 lb (0.17 kg)
32538	5/16", 1/4"	—	—	—	1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16"	—	—	Red	0.37 lb (0.17 kg)
32539	5/16", 1/4"	—	—	—	0.9 mm, 1.3 mm, 1.5 mm, 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	—	—	Blue	0.37 lb (0.17 kg)

Schrader® is a registered trademark of Schrader-Bridgeport International, Inc., TORX® is a registered trademark of Acument Intellectual Properties, LLC.

Magnetic Screwdriver Bit Sets

Non-Ratcheting Magnetic Screwdriver with 32-Piece Tamperproof Bit Set

- Sturdy bit and screw holding magnet allows for screws to fit securely in place for easy use
- Durable PVC black block allows for easy storage of standard 1/4" bits
- Includes complete tamperproof bit set in block



32510



TAMPERPROOF BIT SET INCLUDED WITH SET, ALSO SOLD SEPARATELY 32525



STANDARD BIT SET SOLD SEPARATELY 32526

Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	TORX® Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32510	1/4"	—	—	—	3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	T7, T8, T10, T15, T20, T25, T27, T30, T40	Spanner: 4, 6, 8, 10; Tri-Wing®: 1, 2; TORQ- SET®: 6, 8, 10	3.5" (88.9 mm)	Yellow/ Black	8" (203.2 mm)	0.71 lb (0.32 kg)

Replacement Bits

Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Square Bits	Hex Bits	TORX® Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32526	—	#0, #1, #2, #3	3-4, 5-6, 6-8, 8-10, 10-12, 12-14 Screw Sizes	#1, #2, #3	2mm, 3/32", 7/64", 1/8", 9/64", 4mm, 3/16"	T6, T7, T8, T10, T15, T20, T25	Clutch: 5/32" (4 mm), 3/16" (4.8 mm)	—	—	1" (25.4 mm)	0.43 lb (0.20 kg)
32525	—	—	—	—	5/64" (2 mm), 3/32" (2.4 mm), 7/64" (2.8 mm), 1/8" (3.2 mm), 9/64" (3.6 mm), 5/32" (4.0 mm), 3/16" (4.8 mm), 2 mm, 2.5 mm, 3 mm, 4 mm, 5 mm	T7, T8, T10, T15, T20, T25, T27, T30, T40	Spanner: 4, 6, 8, 10; Tri-Wing®: 1, 2, 3, 4	—	—	1" (25.4 mm)	0.43 lb (0.20 kg)

TORX® is a registered trademark of Acument Intellectual Properties, LLC. TORQ-SET® and Tri-Wing® are registered trademarks of Phillips Screw Co.

See page 297 for additional information on warnings.



Additional and replacement bits can be found on page 60

Multi-Bit Screwdriver/Nut Driver Replacement Parts and Bits

Replacement Parts for Multi-Bit Screwdriver/Nut Drivers

- Precision-machined tips for exact fit into fastener



32398



32396



32397



32484



32478



32784



32781



13105

Cat. No.	Tip Type	For Use With	Package Quantity
32392	—	Heavy Duty (32557) and Ratcheting (32558)	1 Piece
32394	—	Heavy Duty (32557) and Ratcheting (32558)	2 Piece
32395	—	Extended Reach Drivers (32559 and 32560)	1 Piece
32396	—	Stubby Drivers (32561 and 32562)	1 Piece
32397	#2 Phillips; #1 Square	Heavy Duty (32557) and Ratcheting (32558)	2 Bits
32398	#1 Phillips; 1/4" (6.4 mm) Slotted	Heavy Duty (32557), Ratcheting (32558) and Stubby (32561)	2 Bits
32399	#2 Square; 3/16" (4.8 mm) Slotted	Heavy Duty (32557) and Ratcheting (32558)	2 Bits
32400	#1, #2 Phillips	Extended Reach (32559)	2 Bits
32401	3/16" (4.8 mm), 1/4" 6.4 mm) Slotted	Extended Reach (32559)	2 Bits
32410	#2 Square; #2 Phillips	Stubby Driver (32560)	2 Bits
32411	#1 Square; 1/4" (6.4 mm) Slotted	Stubby Driver (32560)	2 Bits
32412	#2 Phillips; 3/16" (4.8 mm) Slotted	Stubby Driver (32561)	2 Bits
32478	#1 Phillips; 3/16" (4.8 mm) Slotted	5-in-1 (32476)	1 Bit
32479	#2 Phillips; 9/32" (7.1 mm) Slotted	5-in-1 (32476)	1 Bit
32482	#1 Phillips; 3/16" (4.8 mm) Slotted	10-in-1, 11-in-1 and 10-Fold™	2 Bits
32483	#2 Phillips; 1/4" (6.4 mm) Slotted	10-in-1, 11-in-1 and 10-Fold™	2 Bits
32484	#1, #2 Square	10-in-1, 11-in-1 and 10-Fold™	2 Bits
67101	#2 Phillips; 3/16" (4.8 mm) Slotted	2-in-1 Rapi-Driv®, 10-in-1, 11-in-1 and 10-Fold	2 Bits
32540	TT7, TT8 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32541	TT9, TT10 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32542	TT15, TT20 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32543	TT25, TT27 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32544	T6, T7 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32485	T10 and T15 TORX®	10-in-1, 11-in-1 and 10-Fold™	2 Bits
32545	T8, T10 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32546	T25, T27 TORX®	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32547	3/32", 7/64" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32548	5/32", 3/16" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32549	1/6", 5/64" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32550	1/8", 9/64" Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32551	0.9 mm, 1.3 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32552	1.5 mm, 2.0 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32553	2.5 mm, 3.0 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32554	4.0 mm, 5.0 mm Hex	10-in-1, 11-in-1 and 10-Fold™ Multi-bit Drivers	2 Bits
32752	#1, #2 Combo	Combo-Tip Multi-Tool (32505)	2 Bits
32528	Schrader® Valve Core Tool	All Klein Tools 2-in-1, 10-in-1, 11-in-1 and 10-Fold Screwdrivers	1 Bit
32770	#1, #2 Phillips	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32771	#0, #3 Phillips	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32772	#1, #2 Square	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32773	T10, T15 TORX®	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32774	T20, T25 TORX®	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32775	4 mm, 6 mm Slotted	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32776	#1, #2 Combo	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32777	6, 8 Spanner	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32778	10, 12 Spanner	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32779	1/8, 9/64 Hex Pin	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32780	5/32, 3/16 Hex Pin	15-in-1 Screwdrivers (32290, 32291, 32292)	1 Bit
32781	10, 15 Tamperproof	15-in-1 Tamperproof Screwdriver (32291)	1 Bit
32782	20, 25 Tamperproof	15-in-1 Tamperproof Screwdriver (32291)	1 Bit
32783	27, 30 Tamperproof	15-in-1 Tamperproof Screwdriver (32291)	1 Bit
32784	Schrader® Valve Core Tool	15-in-1 HVAC Screwdriver (32292)	1 Bit
13391	#0 Phillips; 3/32" (2.4 mm) Slotted	4-in-1 Electronics Screwdriver (32581, 32585)	2 Bits
13392	#00 Phillips; 1/8" (3.2 mm) Slotted	4-in-1 Electronics Screwdriver (32581, 32585)	2 Bits
13104	T7, T10 Tamperproof TORX®	4-in-1 Electronics Screwdrivers (32581, 32585)	2 Bits
13105	T8, T15 TORX®	4-in-1 Electronics Screwdrivers (32581, 32585)	2 Bits
13231	Schrader® Valve Core Tool; 1/8" (3.2 mm) Slotted	HVAC 8-in-1 Slide Driver™ Screwdriver/Nut Driver (32596) and 11-in-1 Multi-bit Screwdriver (Cat. No. 32527)	1 Bit



Screwdrivers, Nut Drivers and Accessories

Meets or exceeds applicable ASME / ANSI and MIL specifications

Plastic-Handle Screwdrivers

Nickel-chrome, precision-forged and polished blades with black tips

Tough amber plastic handle

Smooth Comfordome® handles fit the palm of the hand comfortably

Chrome-plated shank helps prevent corrosion

Internal flanges provide solid, twist-resistant shaft anchor



Plastic-Handle Screwdrivers

Includes core Plastic-Handle Screwdriver features plus:

- Precision-machined Phillips tips provide a more consistent geometric symmetry to ensure accurate fit and torque without slippage
- Small-diameter cabinet-tip shanks for use in recessed holes or tight places and is well-suited for electrical and telecommunications work
- 35% larger than comparable screwdriver handles, the oversized Bull Driver handles deliver up to 50% extra power to perform tough jobs with minimal effort



Cat. No.	Tip Type	Shank Type	Shank Length	Overall Length	Weight
P18	#1 Phillips	Round	8" (203.2 mm)	11.5" (292.1 mm)	2.4 oz (68 g)
P28	#2 Phillips	Round	8" (203.2 mm)	11.625" (295.3 mm)	3.2 oz (91 g)
P212	#2 Phillips	Round	12" (304.8 mm)	15.625" (396.9 mm)	4.0 oz (113 g)
P202	#2 Phillips	Round	20" (508.0 mm)	24.5" (622.3 mm)	8.8 oz (249 g)
A000	3/32" (2.4 mm) Keystone	Round	1.5" (38.1 mm)	2.875" (73 mm)	0.32 oz (9 g)
A216-3	1/8" (3.2 mm) Cabinet	Round	3" (76.2 mm)	6" (152.4 mm)	0.8 oz (23 g)
A216-4	1/8" (3.2 mm) Cabinet	Round	4" (101.6 mm)	7" (177.8 mm)	0.8 oz (23 g)
A216-6	1/8" (3.2 mm) Cabinet	Round	6" (152.4 mm)	9" (228.6 mm)	0.8 oz (23 g)
A216-8	1/8" (3.2 mm) Cabinet	Round	8" (203.2 mm)	11" (279.4 mm)	0.8 oz (23 g)
A216-10	1/8" (3.2 mm) Cabinet	Round	10" (254.0 mm)	13" (330.2 mm)	0.8 oz (23 g)
A316-4	3/16" (4.8 mm) Cabinet	Round	4" (101.6 mm)	7.625" (193.7 mm)	1.6 oz (45 g)
A316-6	3/16" (4.8 mm) Cabinet	Round	6" (152.4 mm)	9.625" (244.5 mm)	1.6 oz (45 g)
A316-8	3/16" (4.8 mm) Cabinet	Round	8" (203.2 mm)	11.625" (295.3 mm)	2.4 oz (68 g)
A316-10	3/16" (4.8 mm) Cabinet	Round	10" (254.0 mm)	13.625" (346.1 mm)	3.2 oz (91 g)
70155	3/16" (4.8 mm) Cabinet	Round	20" (508.0 mm)	24.5" (622.3 mm)	7.2 oz (204 g)

Bull Driver™ Plastic Handle Screwdrivers

BD284	1/4" (6.4 mm) Keystone	Square	4" (101.6 mm)	8.5" (215.9 mm)	4.0 oz (113 g)
BD306	5/16" (7.9 mm) Keystone	Square	6" (152.4 mm)	11.188" (284.2 mm)	5.6 oz (159 g)
BD308	5/16" (7.9 mm) Keystone	Square	8" (203.2 mm)	13.188" (335 mm)	6.4 oz (181 g)
BD410	3/8" (9.5 mm) Keystone	Square	10" (254.0 mm)	15.188" (385.8 mm)	9.6 oz (272 g)
BD412	3/8" (9.5 mm) Keystone	Square	12" (304.8 mm)	17.188" (436.6 mm)	12.0 oz (340 g)
BD144	1/4" (6.4 mm) Keystone	Round	4" (101.6 mm)	8.5" (215.9 mm)	4.0 oz (113 g)
BD146	1/4" (6.4 mm) Keystone	Round	6" (152.4 mm)	10.5" (266.7 mm)	4.0 oz (113 g)
BD156	5/16" (7.9 mm) Keystone	Round	6" (152.4 mm)	11.188" (284.2 mm)	5.6 oz (159 g)
BD408	3/8" (9.5 mm) Keystone	Round	8" (203.2 mm)	13.188" (335 mm)	8 oz (227 g)
BD111	#1 Phillips	Round	3" (76.2 mm)	6.625" (168.3 mm)	1.6 oz (45 g)
BD122	#2 Phillips	Round	4" (101.6 mm)	8.5" (215.9 mm)	3.2 oz (91 g)
BD133	#3 Phillips	Round	6" (152.4 mm)	11.188" (284.2 mm)	5.6 oz (159 g)

Cat. No.	Set Contains	Weight
85276	7 Piece Combination Screwdriver Set	1.1 lb (0.5 kg)

Cat. No. Description

BD284	1/4" Keystone Screwdriver 4" Square Shank
BD306	5/16" Keystone Screwdriver 6" Shank
A216-3	1/8" Cabinet Tip Screwdriver 3" Shank
A216-4	1/8" Cabinet Screwdriver 4" Round Shank
A216-6	Screwdriver, 1/8" Cabinet Tip, 6"
BD111	#1 Profilated Phillips Screwdriver, 3" Shank
BD122	Profilated #2 Phillips Screwdriver 4"

See page 297 for additional information on warnings.

