## Tapping Tools

### **Cushion-Grip Multi-Bit Tap Tool Driver**

- Increases job speed by combining taps and drivers in one tool
- Each tap size rethreads to next larger size if threads are stripped



				32518				
Cat. No.	Nut Driver Sizes	Phillips Bits	Slotted Bits	Other Bits	Shank Length	Handle Color	Overall Length	Weight
32517	1/4", 5/16", 3/8"	#1, #2	1/4" (6.4 mm), 3/16" (4.8 mm)	Taps: 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	4" (101.6 mm)	Yellow/Black	7.75" (196.9 mm)	0.50 lb (0.23 kg)

# Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions Each tap size rethreads to next larger size if threads are stripped

**Cushion-Grip 6-in-1 Tap Tool** 



Cat. No.	Tap Sizes	Overall Length	Weight
626	6-in-1 Tap 6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7.75" (196.9 mm)	0.25 lb (0.11 kg)

### 6-in-1 Tapping Tool

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped
- Two high-carbon steel taps are secured in reversible holder

Cat. No.	Tap Sizes	Overall Length	Weight
627-20	6-32, 8-32, 10-32, 10-24, 12-24, 1/4-20	7.625" (193.7 mm)	0.35 lb (0.16 kg)



626-32 (6-32, 8-32, 10-32)



#### **Triple Taps**

- Quickly forms new threads, re-forms burred threads, and cleans out plaster obstructions
- Each tap size rethreads to next larger size if threads are stripped

Cat. No.	Tap Sizes	Overall Length	Weight
625-24	6-32, 8-32, 10-24	7.125" (181 mm)	0.20 lb (0.09 kg)
625-32	6-32, 8-32, 10-32	7.125" (181 mm)	0.20 lb (0.09 kg)



See page 297 for additional information on warnings.

