



## Pump Pliers

### Klaw™ Pump Pliers

- Compact, narrow design for easy work in small or hard to reach spaces
- Gripping surfaces with specially hardened teeth for reduced wear and positive gripping
- Extended grips for added comfort
- **Quick-Adjust Pump Pliers:** Push button and quick ratchet feature allows for fast and easy adjustment to any position. (Cat. Nos. D504-10B, D504-12B)



D504-10



Cat. No.	Overall Length	Jaw Capacity	Handle Color	Handle Finish	Weight
<b>Quick-Adjust Klaw™ Pump Pliers</b>					
D504-10B	10.125" (257.2 mm)	2-1/8" (54.0 mm)	Yellow	Plastic-Dipped	0.79 lb (0.36 kg)
D504-12B	12.5" (317.5 mm)	2-3/4" (69.9 mm)	Yellow	Plastic-Dipped	1.2 lb (0.5 kg)
<b>Classic Klaw™ Pump Pliers</b>					
D504-7	7.375" (187.3 mm)	1-3/8" (34.9 mm)	Yellow	Plastic-Dipped	0.34 lb (0.15 kg)
D504-10	9.875" (250.8 mm)	2-1/8" (54.0 mm)	Yellow	Plastic-Dipped	0.81 lb (0.37 kg)
D504-12	12" (304.8 mm)	2-3/4" (69.9 mm)	Yellow	Plastic-Dipped	1.4 lb (0.6 kg)

### Pump Pliers

- Secure tongue and groove design for non-slip grip - even with heavy pressure
- Wide range of versatile jaw positions
- Quick adjust rivet allows one handed, fast and easy adjustment of plier jaws
- TT Series feature split tether ring for securing tool when working at height



D502-6



**SPLIT TETHER RING  
FOR USE WITH TETHER**  
D502-6TT  
D502-10TT  
D502-12TT



Plastic-Dipped



JOURNEYMAN™  
Dual-Material

Cat. No.	Overall Length	Jaw Capacity	Handle Color	Handle Finish	Weight
D502-6	6.5" (165.1 mm)	7/8" (22.2 mm)	Yellow	Plastic-Dipped	0.41 lb (0.19 kg)
D502-6TT	8" (203.2 mm)	7/8" (22.2 mm)	Yellow	Plastic-Dipped	0.41 lb (0.19 kg)
D502-10	10" (254.0 mm)	1-3/4" (44.5 mm)	Yellow	Plastic-Dipped	0.97 lb (0.44 kg)
D502-10TT	11.25" (285.8 mm)	1-3/4" (44.5 mm)	Yellow	Plastic Dipped	0.95 lb (0.43 kg)
D502-12	12.25" (311.2 mm)	2-3/8" (60.3 mm)	Yellow	Plastic-Dipped	1.4 lb (0.6 kg)
D502-12TT	13" (330.2 mm)	2-3/8" (60.3 mm)	Yellow	Plastic Dipped	1.4 lb (0.6 kg)
D502-16	16.25" (412.8 mm)	4-1/4" (108.0 mm)	Yellow	Plastic-Dipped	3.2 lb (1.5 kg)
J502-10	10.25" (260.4 mm)	1-3/4" (44.5 mm)	Yellow/Black	Journeyman	1.0 lb (0.5 kg)



## Slip-Joint Pliers

### Slip-Joint Pliers

- Shear-type cutter for precision wire cutting
- Two versatile jaw positions
- Serrated jaws provide sure-gripping power
- Nickel-chrome plated for long life



D511-6

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Handle Color	Handle Finish	Weight
D511-6	6.563" (166.7 mm)	1.188" (30.2 mm)	1.188" (30.2 mm)	3/8" (9.5 mm)	Blue	Plastic-Dipped	0.39 lb (0.18 kg)
D511-8	8.063" (204.8 mm)	1.375" (34.9 mm)	1.25" (31.8 mm)	7/16" (11.1 mm)	Blue	Plastic-Dipped	0.62 lb (0.28 kg)
D511-10	9.875" (250.8 mm)	1.75" (44.5 mm)	1.375" (34.9 mm)	15/32" (11.9 mm)	Blue	Plastic-Dipped	0.83 lb (0.38 kg)

### Slip-Joint Pliers - Hose Clamp

- Quickly installs and removes spring-tension hose clamps
- Grips with either end or side of jaws for work in confined areas
- Nickel-chrome plated for long life



D514-8

Cat. No.	Overall Length	Jaw Length	Jaw Width	Jaw Thickness	Handle Color	Handle Finish	Weight
D514-8	8.063" (204.8 mm)	1.375" (34.9 mm)	1.25" (31.8 mm)	7/16" (11.1 mm)	Blue	Plastic-Dipped	0.61 lb (0.28 kg)

## Pliers Handles

### Replacement Klein-Koat™ Pliers Handles

- Plastic material for slip-resistant grip and comfort



70

Cat. No.	Size to Fit Pliers	Color	Weight
60	6" (152.4 mm) Long	Red	0.80 oz (22.7 g)
70	7" (177.8 mm) Long	Red	0.10 lb (0.05 kg)
89	8" to 9" (203.2 to 228.6 mm) Long	Red	0.10 lb (0.05 kg)

