



## Pocket Knives

### Compact Pocket Knife

- Lockback secures blade in open position
- Corrosion resistant black aluminum handle
- Reversible thumb stud for easy one-hand opening
- Lanyard hole allows knife to be tethered
- Low-carry pocket clip



44142

Cat. No.	Blade Type	Blade Length	Blade Material	Handle Material	Length Closed	Overall Length	Weight
44142	Drop Point	2.875" (73 mm)	440A Stainless Steel	Aluminum	3.8" (96.5 mm)	6.75" (171.5 mm)	0.14 oz (4.0 g)

### Stainless Steel Compact Knives

- Lockback secures blade in open position
- High-grade stainless steel handle with rosewood inlay
- Lightweight and compact



44032

Cat. No.	Blade Type	Blade Length	Blade Material	Handle Material	Length Closed	Overall Length	Weight
44032	Drop Point	1.625" (41.3 mm)	Stainless Steel	Stainless Steel	2.406" (61.1 mm)	4.25" (108 mm)	1.0 oz (28 g)
44033	Drop Point	2.25" (57.2 mm)	Stainless Steel	Stainless Steel	3" (76.2 mm)	5.25" (133.4 mm)	1.8 oz (51 g)
44034	Drop Point	3" (76.2 mm)	Stainless Steel	Stainless Steel	4" (101.6 mm)	7" (177.8 mm)	4.0 oz (113 g)

### Wood Grain Handle Pocket Knives

- Liner lock secures blade in open position
- Durable plastic handle with faux wood grain
- Shackle allows knife to be tethered



1550-4



1550-11



1550-44

Cat. No.	Blade Type	Blade Length	Blade Material	Handle Material	Length Closed	Overall Length	Weight
1550-4	Hawkbill	2.625" (66.7 mm)	Carbon Steel	Plastic	4.141" (105.2 mm)	6.125" (155.6 mm)	4.0 oz (113 g)
1550-11	Coping	2.25" (57.2 mm)	Carbon Steel	Plastic	3.25" (82.6 mm)	5.5" (139.7 mm)	1.5 oz (43 g)
1550-44	Hawkbill	2.625" (66.7 mm)	Stainless Steel	Plastic	3.5" (88.9 mm)	6.125" (155.6 mm)	4.0 oz (113 g)

### Slitting Pocket Knife

- Liner lock secures blade in open position
- Durable plastic handle
- Shackle allows knife to be tethered



1550-24

Cat. No.	Blade Type	Blade Length	Blade Material	Handle Material	Length Closed	Overall Length	Weight
1550-24	Hawkbill	2.75" (69.9 mm)	Stainless Steel	Plastic	4.5" (114.3 mm)	6.75" (171.5 mm)	2.6 oz (74 g)

See page 297 for additional information on warnings.



**WARNING:** Blades are intended for cutting only, and should be handled and disposed of with care. Bending the blade can cause it to break, possibly resulting in bodily injury. **Check local laws on legality of selling or possessing these knives.**

## Pocket Knives

### Sportsman Knives

- Lockback secures blade in open position
- Wood handle with brass holsters
- Cat. No. 44037 has a leather case with belt loop



44037

Cat. No.	Blade Type	Blade Length	Blade Material	Handle Material	Length Closed	Overall Length	Weight
44036	Clip Point	2.625" (66.7 mm)	Stainless Steel	Ebony Wood	3.75" (95.3 mm)	6.375" (161.9 mm)	2.6 oz (74 g)
44037	Clip Point	3.375" (85.7 mm)	Stainless Steel	Ebony Wood	5" (127.0 mm)	8.75" (222.3 mm)	6.6 oz (187 g)

## Pocket Knives – Multi-Blade

### 2-Blade Pocket Knife - Spearpoint and Screwdriver-Tip Blades

- Standard spearpoint blade - 2-1/2" (63.5 mm) long
- Screwdriver-tip blade - 2-1/2" (63.5 mm) long
- Screwdriver-tip blade locks open



1550-2

Cat. No.	Blade Length	Material	Length Closed	Overall Length	Weight
1550-2	2.5" (63.5 mm)	Carbon Steel	3.75" (95.3 mm)	6.625" (168.3 mm)	4.0 oz (113 g)

### 3-Blade Pocket Knife - Sheepsfoot, Spearpoint and Screwdriver-Tip Blades

- Curved sheepsfoot skinning blade - 2-3/8" (60 mm) long
- Standard spearpoint blade - 2-1/2" (64 mm) long
- Screwdriver-tip blade - 2-1/2" (64 mm) long
- Screwdriver blade locks open



1550-6

Cat. No.	Blade Length	Material	Length Closed	Overall Length	Weight
1550-6	2.375" (60.3 mm), 2.5" (63.5 mm)	Carbon Steel	3.75" (95.3 mm)	6.5" (165.1 mm)	5.0 oz (142 g)