



Conduit Tools

Electrician's Conduit Scoring Tool

- Durable zinc cast scoring tool eliminates spiraling
- Used for scoring 1/2", 3/4" and 1" EMT conduit
- Klein-designed, patented scoring wheel scores and allows clean conduit snaps without leaving burrs inside
- 1" scoring wheel conveniently located in base of the handle; no tools required to replace scoring wheels
- Four roller tracks specifically designed for professional use
- Compact, enclosed design for use on job sites



88906

US Patent: D638451

Cat. No.	Cutting Capacity	Overall Length	Weight
88906	Scores 1/2", 3/4" and 1" (12.7 mm, 19.1 mm and 25.4 mm) EMT Conduit	6" (152.4 mm)	1.3 lb (0.6 kg)



REPLACEMENT BLADES
1/2" & 3/4" — 88907
1" — 88908

Conduit Locknut Wrench

- Easily attach locknuts in tight or deep cut-in boxes
- For 1/2" and 3/4" connectors
- Direct-drive heads rotate each other when twisted
- Heavy-duty steel construction enables needed torque to loosen or tighten connectors
- Perfect for remodel work where box is filled with existing wires



56999

US Patent pending

Cat. No.	Size	Overall Length	Weight
56999	1/2" and 3/4"	9" (228.6 mm)	0.70 lb (0.32 kg)




Fish Tape Pulling Pliers

Includes core side-cutting features plus:

- Easily pulls 1/8" or 1/4" flat steel fish tape without damaging the tape
- Crimps non-insulated connectors, lugs, and terminals (Cat. No. J2000-9NECRTP)



D213-9NETP



Plastic-Dipped



JOURNEYMAN™
Dual-Material

Cat. No.	Jaw Length	Jaw Width	Jaw Thickness	Knife Length	Handle Color	Handle Finish	Overall Length	Weight
D213-9NETP	1.594" (40.5 mm)	1.25" (31.8 mm)	5/8" (15.9 mm)	0.781" (19.8 mm)	Dark Blue	Plastic-Dipped	9.375" (238.1 mm)	1.1 lb (0.5 kg)
J213-9NETP	1.594" (40.5 mm)	1.25" (31.8 mm)	5/8" (15.9 mm)	0.781" (19.8 mm)	Dark Blue/Black	Journeyman	9.5" (241.3 mm)	1.1 lb (0.5 kg)
Pliers with heavy-duty cutting knives designed to cut ASCR, screws, nails and most hardened wire								
D2000-9NETP	1.594" (40.5 mm)	1.25" (31.8 mm)	5/8" (15.9 mm)	0.781" (19.8 mm)	Light Blue	Plastic-Dipped	9.375" (238.1 mm)	1.1 lb (0.5 kg)
J2000-9NETP	1.594" (40.5 mm)	1.25" (31.8 mm)	5/8" (15.9 mm)	0.781" (19.8 mm)	Light Blue/Black	Journeyman	9.5" (241.3 mm)	1.1 lb (0.5 kg)
J2000-9NECRTP	1.594" (40.5 mm)	1.25" (31.8 mm)	1-19/32" (40.5 mm)	0.781" (19.8 mm)	Blue/Black	Journeyman	9.5" (241.3 mm)	1.1 lb (0.5 kg)

See page 297 for additional information on warnings.

