



GRF4C3

by Burndy Catalog ID: GRF4C3

Prop 65 Notice

Univeral Grounding Clamp, 1 or 2 Nos of Conductors, 8 AWG-2 AWG, Pedestal Type : 1" (Round), Upto 7/8" (Square), 3/8" Stud.

Features: One Connector Fits All Applications, Ease Of Specification And Installation, Single Bolt Design, Ease Of Installation: No Need To Disassemble, Single Wrench Installation, Accepts 1 Or 2 Ground Conductors, Requires Less Connectors To Install Signal Reference Grid, Tin Plated Cast Bronze Construction, Resists Corrosion And Provides Extended Life Ground Connection, Grounds All Pedestals (Round Or Square), Will Handle Up To 7/8 IN Square And 1 IN Round, Ease Of Installation, One Connector Does It All, Serves 3 Needs: 1. Signal Reference Grid, 2. Static Ground, 3. Fault Current Ground, UNIGROUND Solves All Possible Grounding Problems Found In Computer Applications Today, UL467 Listed, Installation Torque: 240 IN-LB, Width: 1.76 IN, Height: 3.14 IN, Dimension B: 1.96 IN, Pedestal Type: For Round Up To 1 IN, For Square Up To 7/8 IN

Product Details

General

Application	For Raised Floor Systems
Installation Torque Recommended in-Ib	100 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	UNIGROUND
Trade Name	UNIGROUND™
Туре	GRF
UPC	781810828021
UPC 12 Digit	7818108280211

Dimensions

Dimension - B Length inch	1.96 in
Dimension - Height inch	3.14 in
Dimension - Width inch	1.76 in
Dimension - Width mm	45 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	8 AWG-2 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	8 AWG-2 AWG
Conductor - Pipe or Round Tube Size	3/8 ;1/2 ;3/4 ;1

Conductor - Pipe or Round Tube Size Range	3/8 in -1 in
Conductor - Pipe or Square Tube Size	1/2 ;5/8 ;3/4 ;7/8
Conductor - Pipe or Square Tube Size Range	1/2 in -7/8 in
Number Of Conductors	1;2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity 1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)