



GD184C

by Burndy Catalog ID: GD184C

Prop 65 Notice

Mechanical Grounding Connector, 2 Parallel Cables to Rod or Pipe, 8 AWG (Sol.) - 4 AWG (Str.), 2" to 2-3/8" Rod, 2" Pipe.

Features: High Copper Alloy Ground Connector For Joining A Range Of Two Parallel Cables To Rod Or Pipe, Especially Good For Grounding Fence Posts, High Copper Alloy Cast Body With DURIUM U-Bolts, Nuts, And Lockwashers Make The GD Suitable For Burial In Ground Or Concrete, One-Wrench Installation, UL467 Listed, Acceptable For Direct Burial In Earth Or Concrete, Raised Floor: No, Ground Rod Size: 2 - 2-3/8 IN, Tube (ips) Size: 2 IN, Width: 3-3/4 IN, Installation Torque: 240 IN-LB, Height: 4-3/8 IN

Product Details

General

Application	For Joining A Range Of Two Parallel Copper Cables To Rod Or Pipe And Burial In Ground Or Concrete
Installation Torque Recommended in-Ib	240 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	Ν
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Туре	GD
U Bolt Type	259
UPC	781810260326
UPC 12 Digit	7818102603266

Dimensions

Dimension - B Length inch	1.31 in
Dimension - Height fraction	4-3/8 in
Dimension - Height inch	4.38 in
Dimension - Width fraction	3-3/4 in
Dimension - Width inch	3.69 in
Dimension - Width mm	94 mm

Conductor Related

Conductor - Copper Solid Size	8;7;6;5;4
Conductor - Copper Solid Size Range	8-4
Conductor - Copper Str Size	8;7;6;5;4
Conductor - Copper Str Size B Range	2
Conductor - Copper Str Size Range	8-4
Conductor - Copper Tube Std Size	2

Conductor - Copper Tube Std Size Range	2
Conductor - Rod Size	2 in
Conductor - Rod Size Range	2 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity

6

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)