



KS17

by Burndy
Catalog ID: KS17

Prop 65 Notice

Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap), Length: 1.14.

Features: UL467 Listed For Direct Burial Applications In Earth Or Concrete, Compact, High-Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Cracking And Corrosion, Conductor Type: Run And Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Type D Copperweld, Stranded Copperweld, Type A Copperweld, Installation Torque: 165 IN-LB, Length: 1.14 IN, Cross Flats: 0.63 IN, Width: 0.45 IN

Product Details

General

Application	For Direct Burial Applications In Earth Or Concrete, Copper
Connector Type	Split Bolt
Installation Torque Recommended in-lb	165 in
Material	Copper
Operating Temperature Celcius Max	90 °C
Operating Temperature Celcius Min	0 °C
Operating Temperature Range Celcius	0 - 90
Operating Temperature Range Fahrenheit	32 - 194
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS, Compact
UPC	781810011508
UPC 12 Digit	7818100115088

Dimensions

Dimension - B Length fraction	29/50 in
Dimension - B Length inch	.58 in
Dimension - Cross Flats inch	0.63 in
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.14
Dimension - Width fraction	9/20 in
Dimension - Width inch	0.45 in
Dimension - Width mm	11 mm
Width	0.45 in

Conductor Related

Conductor - Copper Solid Run	6 AWG
------------------------------	-------

Conductor - Copper Solid Run Range	8 AWG-6 AWG
Conductor - Copper Solid Tap	6 AWG
Conductor - Copper Solid Tap Range	14 AWG-6 AWG
Conductor - Copper Str Run	8 AWG;7 AWG;6 AWG
Conductor - Copper Str Run Range	8 STR - 6 STR
Conductor - Copper Str Tap	14 AWG;12 AWG;10 AWG;9 AWG;8 AWG;7 AWG;6 AWG
Conductor - Copper Str Tap Range	8 STR - 6 STR
Conductor - CopperWeld Solid Run	6 AWG
Conductor - CopperWeld Solid Run Range	6 AWG
Conductor - CopperWeld Solid Tap	6 AWG
Conductor - CopperWeld Solid Tap Range	6 AWG
Conductor - CopperWeld Str Run	9-1/2D ;8A ;3#12
Conductor - CopperWeld Str Run Range	9-1/2D -3#12
Conductor - CopperWeld Str Size	9-1/2 D;8A ;3#12
Conductor - CopperWeld Str Size Range	9-1/2 D-3#12
Conductor - CopperWeld Str Tap	9-1/2 D;8A ;3#12
Conductor - CopperWeld Str Tap Range	9-1/2 D-3#12
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	RUS
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)